

HP

Jornada 600 Series

Handheld PCs

## The compact PC companion for greater on-the-go productivity

At Hewlett-Packard, we know that it's not just the destination, but the journey that matters. We believe that a PC companion is not simply a tool to help you with your **day's work**—but also a personal **journal** or daily record, a place for you to plan your day, a companion to take with you on a **journey**.

The **HP Jornada 600 Series Handheld PC** was designed with these ideas in mind—a convenient and versatile PC companion that's prepared for *any* journey. The HP Jornada provides all the tools you need to manage e-mail and personal information while you're mobile, and to access and capture the information you need whenever and wherever you need it.

### Compact, convenient, and ready to work when you are

Small enough to drop into your handbag or coat pocket, and light enough to carry anywhere, the HP Jornada allows you to work for up to **eight hours<sup>1</sup> without recharging**. With preloaded pocket versions of **Microsoft Word, Excel, PowerPoint, and Access**, you have all the familiar tools you need to be productive on the go. And no matter where you take the HP Jornada—and what the lighting conditions—you'll find it easy to view important information on its **brilliant color screen**.

### No-hassle mobile e-mail and personal information management

The HP Jornada is the perfect mobile solution for e-mail and Web browsing with its built-in **56Kbps modem<sup>2</sup>** and preloaded **Microsoft Pocket Inbox and Pocket Internet Explorer**. If you're just getting started, special **HP dialup software** can help you set up your modem connections. And to make managing your personal information—including your schedule, contacts, and to-do lists—easier than ever, the HP Jornada also includes an enhanced version of **Microsoft Pocket Outlook**.

### Fast access and capture of important business information

The **instant-on** feature and **programmable quick launch keys** allow you to access critical information with the touch of a button. And HP's special **viewer software** lets you view your contact and schedule information at a glance. Quickly capture information and convert it into contact, e-mail, and appointment records automatically with HP's **quick pad** application. And to make entering data even easier, the HP Jornada features a **roomy, touch-typeable keyboard** that is 76% of the size of your desktop PC keyboard!



- Lightweight and compact—fits in your coat pocket or handbag
- Work up to 8 hours<sup>1</sup> without recharging
- Stay in touch wherever you go with internal 56Kbps modem<sup>2</sup>

### New! HP Jornada 690 Handheld PC

- 32MB RAM for greater storage capacity and productivity
- Microsoft® ActiveSync® and Outlook 2000 (desktop version)<sup>3</sup> included FREE!

### Smooth integration with your PC and back-office infrastructure

Like all HP handheld PCs, the HP Jornada is fully compliant with the **Desktop Management Interface (DMI) standard**, making it easier for your MIS department to manage it as part of their mobile PC inventory. Working in the familiar Windows environment allows you to be productive right away—without any special training—using **Microsoft Windows® CE, Handheld PC Professional Edition software**. And **Microsoft synchronization software** ensures the files on your desktop and handheld PC are always up-to-date.

<sup>1</sup> Estimated battery life. Actual battery life will vary based on usage.

<sup>2</sup> Model with internal modem may not be available in some countries. Please check with your reseller for details. This 56Kbps modem is designed to be capable of receiving data at up to 56Kbps from a compatible service provider and transmitting data at up to 31.2Kbps. Public networks currently limit maximum download speeds to about 53Kbps. Actual speeds depend on many factors and are often less than the maximum possible. Complies with v.90 ITU 56K specification.

<sup>3</sup> Microsoft Outlook 2000 is not available in Portuguese or Chinese.

## HP Jornada 600 Series Handheld PCs

HP Jornada 690 Handheld PC		HP Jornada 680 Handheld PC	
<b>Part Number</b>	<ul style="list-style-type: none"> <li>HP Jornada 690 (HP F1813A—with internal modem)</li> <li>HP Jornada 690e (HP F1814A—without internal modem)</li> </ul>	<b>Part Number</b>	<ul style="list-style-type: none"> <li>HP Jornada 680 (HP F1262A—with internal modem)</li> <li>HP Jornada 680e (HP F1263A—without internal modem)</li> </ul>
<b>CPU</b>	<ul style="list-style-type: none"> <li>133MHz 32-bit Hitachi SH3 processor</li> </ul>	<b>CPU</b>	<ul style="list-style-type: none"> <li>133MHz 32-bit Hitachi SH3 processor</li> </ul>
<b>Included Software (in ROM)</b>	<ul style="list-style-type: none"> <li>Microsoft Windows CE, Handheld PC Professional Edition</li> <li>Microsoft Pocket Word, Excel, PowerPoint, and Access</li> <li>Microsoft Pocket Outlook (Calendar, Tasks, Contacts, Inbox)</li> <li>Microsoft Pocket Internet Explorer</li> <li>HP Jornada viewer, dialup, settings, show, backup, hot keys, quick pad, macro, power, country selector</li> <li>LandWare OmniSolve™<sup>1</sup> (business calculator)</li> <li>BSQUARE bFIND™<sup>2</sup> (search utility)</li> <li>BSQUARE bFAX™ Pro<sup>3</sup> (send/receive faxes)</li> </ul>	<b>Included Software (in ROM)</b>	<ul style="list-style-type: none"> <li>Microsoft Windows CE, Handheld PC Professional Edition</li> <li>Microsoft Pocket Word, Excel, PowerPoint, and Access</li> <li>Microsoft Pocket Outlook (Calendar, Tasks, Contacts, Inbox)</li> <li>Microsoft Pocket Internet Explorer</li> <li>HP Jornada viewer, dialup, settings, show, backup, hot keys, quick pad, macro, power, country selector</li> <li>LandWare OmniSolve™ (business calculator)</li> <li>BSQUARE bFIND™ (search utility)</li> <li>BSQUARE bFAX™ Pro<sup>3</sup> (send/receive faxes)</li> </ul>
<b>Included Software (on CD-ROM)</b>	<ul style="list-style-type: none"> <li>Microsoft ActiveSync (PC synchronization), Outlook 2000 (full retail desktop version), PowerPoint Viewer/Converter</li> <li>Starfish™ TrueSync™ CE 2.0<sup>4</sup> (synchronize with REX™ cards)</li> <li>Trio™ PhoneManager 2.0<sup>5</sup> (send/receive SMS messages and manage your phonebook with a GSM cellular phone)</li> <li>Inso™ Outside In™<sup>1</sup> (view e-mail attachments in multiple formats)</li> <li>On the Go Software™ Pocket Quicken™ 2.1<sup>1</sup> (manage your personal finances and synchronize files with desktop Quicken)</li> <li>WESTTEK™ JETCET™ PRINT HP Lite and JETCET Print 2.0 trial copy<sup>1</sup> (print color documents)</li> <li>Sierra Imaging Image Expert™ CE 2.0<sup>6</sup> (view, edit, and communicate digital images)</li> </ul>	<b>Included Software (on CD-ROM)</b>	<ul style="list-style-type: none"> <li>Microsoft Windows CE Services 2.2 (PC synchronization), PowerPoint Viewer/Converter</li> <li>Starfish TrueSync CE 2.0<sup>4</sup> (synchronize with REX cards)</li> <li>Trio PhoneManager 2.0<sup>5</sup> (send/receive SMS messages and manage your phonebook with a GSM cellular phone)</li> <li>Inso Outside In (view e-mail attachments in multiple formats)</li> <li>On the Go Software Pocket Quicken 2.1<sup>1</sup> (manage your personal finances and synchronize files with desktop Quicken)</li> <li>WESTTEK JETCET PRINT HP Lite and JETCET Print 2.0 trial copy<sup>1</sup> (print color documents)</li> <li>Sierra Imaging Image Expert CE 2.0<sup>6</sup> (view, edit, and communicate digital images)</li> </ul>
<b>Display</b>	<ul style="list-style-type: none"> <li>6.5-in (16.7-cm) color LCD display (supports up to 65,536 colors)</li> <li>640 × 240 pixels on screen, 0.23mm dot pitch</li> <li>1024 × 768 pixels on external monitor (with optional VGA Out PC Card)</li> </ul>	<b>Display</b>	<ul style="list-style-type: none"> <li>6.5-in (16.7-cm) color LCD display (supports up to 65,536 colors)</li> <li>640 × 240 pixels on screen, 0.23mm dot pitch</li> <li>1024 × 768 pixels on external monitor (with optional VGA Out PC Card)</li> </ul>
<b>Input</b>	<ul style="list-style-type: none"> <li>Large (76% full-size) keyboard</li> <li>Embedded numeric keypad</li> <li>Touch screen</li> </ul>	<b>Input</b>	<ul style="list-style-type: none"> <li>Large (76% full-size) keyboard</li> <li>Embedded numeric keypad</li> <li>Touch screen</li> </ul>
<b>Memory</b>	<ul style="list-style-type: none"> <li>32MB SDRAM</li> <li>Burst Mode ROM; user upgradable</li> </ul>	<b>Memory</b>	<ul style="list-style-type: none"> <li>16MB SDRAM; user upgradable</li> <li>Burst Mode ROM; user upgradable</li> </ul>
<b>Communications</b>	<ul style="list-style-type: none"> <li>High-performance internal modem 56Kbps, v.90<sup>7</sup></li> <li>Internet e-mail support: POP3, IMAP4, SMTP, and LDAP</li> <li>E-mail attachment support</li> </ul>	<b>Communications</b>	<ul style="list-style-type: none"> <li>High-performance internal modem 56Kbps, v.90<sup>7</sup></li> <li>Internet e-mail support: POP3, IMAP4, SMTP, and LDAP</li> <li>E-mail attachment support</li> </ul>
<b>Card Slot</b>	<ul style="list-style-type: none"> <li>One PC Card Type II card slot</li> <li>One CompactFlash Type I card slot</li> </ul>	<b>Card Slot</b>	<ul style="list-style-type: none"> <li>One PC Card Type II card slot</li> <li>One CompactFlash Type I card slot</li> </ul>
<b>External Ports</b>	<ul style="list-style-type: none"> <li>One RS232C serial port, 115Kbps</li> <li>One IrDA port, 115Kbps</li> <li>One RJ11 modem port</li> </ul>	<b>External Ports</b>	<ul style="list-style-type: none"> <li>One RS232C serial port, 115Kbps</li> <li>One IrDA port, 115Kbps</li> <li>One RJ11 modem port</li> </ul>
<b>Sound</b>	<ul style="list-style-type: none"> <li>Audio speaker and microphone</li> <li>Built-in voice recording</li> </ul>	<b>Sound</b>	<ul style="list-style-type: none"> <li>Audio speaker and microphone</li> <li>Built-in voice recording</li> </ul>
<b>Power</b>	<ul style="list-style-type: none"> <li>Rechargeable Lithium Ion battery</li> <li>One 3V CR2032 coin-cell backup battery</li> <li>AC adapter</li> <li>Up to 8 hours<sup>8</sup> of battery life</li> </ul>	<b>Power</b>	<ul style="list-style-type: none"> <li>Rechargeable Lithium Ion battery</li> <li>One 3V CR2032 coin-cell backup battery</li> <li>AC adapter</li> <li>Up to 8 hours<sup>8</sup> of battery life</li> </ul>
<b>Physical Specifications</b>	<ul style="list-style-type: none"> <li>7.4 × 3.7 × 1.3 in (18.9 × 9.5 × 3.4 cm)</li> <li>1.1 lbs (510 g) with standard battery</li> </ul>	<b>Physical Specifications</b>	<ul style="list-style-type: none"> <li>7.4 × 3.7 × 1.3 in (18.9 × 9.5 × 3.4 cm)</li> <li>1.1 lbs (510 g) with standard battery</li> </ul>
<b>Other Standard Features</b>	<ul style="list-style-type: none"> <li>LEDs (appointments, recording, and charging)</li> <li>Docking cradle</li> <li>Synchronization cable</li> </ul>	<b>Other Standard Features</b>	<ul style="list-style-type: none"> <li>LEDs (appointments, recording, and charging)</li> <li>Docking cradle</li> <li>Synchronization cable</li> </ul>
<b>Operating Requirements</b>	<ul style="list-style-type: none"> <li>Operating temperature: 32–104° F (0–40° C)</li> <li>Storage temperature: 32–140° F (0–60° C)</li> <li>Humidity: 90% relative humidity at 104° F (40° C)</li> </ul>	<b>Operating Requirements</b>	<ul style="list-style-type: none"> <li>Operating temperature: 32–104° F (0–40° C)</li> <li>Storage temperature: 32–140° F (0–60° C)</li> <li>Humidity: 90% relative humidity at 104° F (40° C)</li> </ul>
<b>Warranty</b>	<ul style="list-style-type: none"> <li>One-year parts-and-labor HP Customer Care standard warranty</li> </ul>	<b>Warranty</b>	<ul style="list-style-type: none"> <li>One-year parts-and-labor HP Customer Care standard warranty</li> </ul>

<sup>1</sup> Available for North America, Europe, Latin America, and Asia Pacific (English-only) options. Trio PhoneManager is downloadable from the Web for U.S. users.

<sup>2</sup> Microsoft Outlook 2000 is not available in Portuguese or Chinese.

<sup>3</sup> Available in English only.

<sup>4</sup> Available for U.S. only.

<sup>5</sup> Model with internal modem may not be available in some countries. Please check with your reseller for details. This 56Kbps modem is designed to be capable of receiving data at up to 56Kbps from a compatible service provider and transmitting data at up to 31.2Kbps. Public networks currently limit maximum download speeds to about 53Kbps. Actual speeds depend on many factors and are often less than the maximum possible. Complies with v.90 ITU 56K specification.

<sup>8</sup> Estimated battery life. Actual battery life may vary based on usage.

## HP Jornada 600 Series Handheld PC Accessories

- 16MB Expansion RAM (F1285A)—for expanding Jornada 680 to 32MB
- Sync Cable (F1258A)\*
- Docking Cradle (F1278A)\*
- Parallel Printer Cable (F1274A)
- Serial Adapter (F1295A)
- AC Adapter (F1279A)\*
- Standard Battery (F1281A)\*
- Extended Battery (F1282A)
- External Charger (F1284)
- External Keyboard (F1275A) (U.S. English only)
- Leather Case (F1227A)
- VGA Out PC Card (F1252A)
- Stylus (2-pack) (F1280A)

\* Included with product



Microsoft, Windows, the Windows CE logo, and ActiveSync are either registered trademarks or trademarks of Microsoft Corporation in the United States and/or other countries. OmniSolve is a trademark of LandWare, Inc. bFIND and bFAX Pro are trademarks or registered trademarks of BSQUARE Corporation. Starfish and TrueSync are trademarks of Starfish Software. REX is a trademark of Franklin Electronic Publishers. Trio is a registered trademark of Trio AB. Inso and Outside In are registered trademarks of Inso Corporation in the United States and/or other countries. Quicken is a registered trademark of Intuit Inc. in the United States and/or other countries used by On the Go Software under license. On the Go Software is a registered trademark of On the Go Software, Inc. WESTTEK and JETCET are trademarks of WESTTEK, L.L.C. Image Expert is a registered trademark of Sierra Imaging. All other brands and product names are trademarks or registered trademarks of their respective companies.

In a continuing effort to improve the quality of our products, technical and environmental information in this document is subject to change without notice.

© Copyright Hewlett-Packard Company 1999

All Rights Reserved. Reproduction, adaptation, or translation without prior written permission is prohibited, except as allowed under the copyright laws.

Printed in XXX 11/99  
XXXX-XXXX

Powered by



Microsoft  
Windows CE  
Handheld PC

To learn more about the HP Jornada 600 Series Handheld PCs, please visit us on the Web at [www.hp.com/jornada](http://www.hp.com/jornada).