





Digital ABS Caliper Nib Style/Std. Jaws

Item number: 551-331-20

Images



Dust- and
Water-
Protected

www.tuv.com
ID 000045042

Description


This is a Digimatic caliper with nib-style and standard jaws.
It offers you the following benefits:

- Knife-shaped measuring surfaces allow you to take outside measurements.
- Rounded measuring surfaces enable you to measure inside dimensions.
- ABSOLUTE System delivers reliable measurements.

Features

Delivered:	In a box with SR44 battery
Digital/Analog:	Digital
Inch-Metric:	Metric
Range:	0 - 300 mm
Inside measuring from:	10.1 mm
Max. Permissible Error E MPE:	±0,04 mm
Max. Permissible Error S MPE:	±0,04 mm
OFFSET:	10 mm
Digital step:	0,01 mm
Max. response speed:	Unlimited
Display:	LCD, character height 9 mm (200 mm) 11 mm (300 mm) 10 mm (>300 mm)
Remarks:	IP67
Battery life:	Approx. 5 years under normal use
ORIGIN (ABS-Zero):	Yes
PRESET:	Yes
Auto Power OFF after 20 min. non use:	Yes
Low voltage alarm:	Yes
Data output:	Yes
Mass:	400 g

Dimensions



b: 40 mm

c: 32.2 mm

d: 90 mm

g: 5 mm

s: 10 mm

h: 20 mm

t: 3.8 mm

R: 5 mm

Accessories

Optional accessories:

Mitutoyo

MiCAT
the standard in world
metrology software
MeasurLink

USB-ITPAK Vers. 3.0

USB Dongle + Manual (Software available
Online)

Art No. 06AGR543

Suggested retail price: **340.00 €***

**Digimatic Cable with Data Button IP Type**

2m, Caliper Type

Art No. 05CZA625

Suggested retail price: **107.00 €***

**Digimatic Cable with Data Button IP Type**

1m, Caliper Type

Art No. 05CZA624

Suggested retail price: **100.00 €***

**USB Input Tool Direct (Digimatic to USB)**

2m Cable, Digimatic/Digimatic 2, with Data
Button IP Caliper Type

Art No. 06AFM380A

Suggested retail price: **141.00 €***

**U-WAVE fit, IP67 Type**

Wireless Transmitter for Caliper

Art No. 264-620

Suggested retail price: **185.00 €***

**U-WAVE fit, Buzzer Type**

Wireless Transmitter for Caliper
Art No. 264-621
Suggested retail price: **185.00 €***

**U-WAVE fit Bluetooth, IP67 Type**

Wireless Transmitter for Caliper
Art No. 264-624
Suggested retail price: **185.00 €***

**U-WAVE fit Bluetooth, Buzzer Type**

Wireless Transmitter for Caliper
Art No. 264-625
Suggested retail price: **185.00 €***

**Connection Unit for IP Caliper, Micrometer**

with Data Button for U-WAVE fit, U-WAVE fit Bluetooth
Art No. 02AZF310
Suggested retail price: **110.00 €***

Spare parts

Consumable spares:



Battery SR44 1,5 V

Art No. 938882

Suggested retail price: 7.00 €*
