


**IB-DK4040a-CPD**
**Article no.** 61144 **EAN code** 4250078174783

# 10-in-1 USB Type-C® Notebook Docking Station

The 10-in-1 USB Type-C® Docking Station is designed to meet all your connectivity needs, whether you're at home or on the go. The IB-DK4040a-CPD supports dual video outputs, card reading capabilities, and various USB interfaces, making it adaptable to all your needs anytime and anywhere. Its versatile design makes it perfect for both home and travel use. The durable construction ensures long-lasting reliability, while its compact size allows for easy carrying and integration into any setup.


**Host**

 Supports USB 3.2  
Gen 1 Type-C®

**Display**

 1x HDMI® 4K@60 Hz,  
1x VGA 2K@60 Hz

**USB interfaces**

 3x USB 3.2 Gen 1 Type-A (5 Gbit/s)  
1x USB 3.2 Gen 1 Type-C® (5 Gbit/s)

**Power Delivery**

 USB Type-C® PD 3.0  
up to 100 W


**LAN Port**

RJ45 Gigabit Ethernet


**Card Reader**

SD/microSD, Multi-LUN

## VIEWS



## KEY FEATURES



### Dual video output

The IB-DK4040a-CPD offers a dual video output that can display both HDMI® and VGA simultaneously at a resolution of up to 2K@60 Hz. For single HDMI® output, users can enjoy resolutions of up to 4K@60 Hz. This allows you to choose the optimal display settings for your needs, whether for detailed graphics or everyday use.



### Multi-connectivity options

Equipped with multiple USB ports and SD/microSD slots, the IB-DK4040a-CPD offers a wide range of connectivity options and easy access to your files, as well as support for the Multi-LUN feature for memory cards. Whether you are transferring files from your device or photos from your memory cards, the IB-DK4040a-CPD meets all your needs.



### Travel-friendly

Made from high-quality aluminium, the IB-DK4040a-CPD combines durability with a light-weight design, making it an ideal companion for travel. Its solid build resists wear and tear, while its compact size fits easily into your bag, providing reliable connectivity wherever your journey takes you.

## VERPACKUNGSIHALT

- ▶ 1x IB-DK4040a-CPD
- ▶ 1x Manual

## PRODUCT FEATURES

Colour	Material	UASP support	Cable length	Video technology
Silver/black	Aluminium/ABS+PC	Yes	20 cm (integrated)	DisplayPort Alt Mode

## VIDEO CONNECTION AND DISPLAY OUTPUT MATRIX

Video matrix, maximum resolutions		
Number of displays	Input (plug-in)	Output
	HDMI®	VGA
Single video output	3840x2160@60 Hz	
		1920x1080@60 Hz
Dual video output	1920x1080@60 Hz	1920x1080@60 Hz

## SYSTEM REQUIREMENTS

Supported Operating Systems	Host compatibility
Windows®/macOS®	USB Type-C® has to support DisplayPort Alt Mode for HDMI® Power supply is not included

## INTERFACE TO HOST COMPUTER

Port	Position	Version & transfer rate	Features
1x USB Type-C®	Right side (integrated cable)	USB 3.2 Gen 1 (5 Gbit/s)	Supports PD 3.0 up to 20 V/5 A (100 watts)

## USB CONNECTIONS

Port	Position	Version & transfer rate	Wattage
3x USB Type-A	Front	USB 3.2 Gen 1 (5 Gbit/s)	<2 W
1x USB Type-C®	Front	USB 3.2 Gen 1 (5 Gbit/s)	<2 W

## FURTHER IN-/OUTPUTS

Port	Position	Features	Wattage
1x USB Type-C®	Rear	Power Delivery 3.0	Up to 100 watts
1x RJ45	Rear	10/100/1000 Mbit/s	-
1x SD card reader	Front	Supports SDXC, SDHC, SD, MMC, RS-MMC	-
1x microSD card reader	Front	Supports microSDHC, microSDXC	-

## NEW USB NOMENCLATURE

Legacy USB Standards	Current USB Standards	Data transfer rate
USB 3.0 = USB 3.1 (Gen 1)	= USB 3.2 Gen 1	= 5 Gbit/s
USB 3.1 = USB 3.1 (Gen 2)	= USB 3.2 Gen 2	= 10 Gbit/s
USB 3.2 (Gen 2x2)	= USB 3.2 Gen 2x2	= 20 Gbit/s
	= USB4® Gen 2x1	= 10 Gbit/s
	= USB4® Gen 2x2	= 20 Gbit/s
	= USB4® Gen 3x2	= 40 Gbit/s

## LOGISTIC DATA

Packing unit	Total weight	Gross weight (with packing)	Net weight	Dimension/ carton	Dimension (with packing)	Dimension of article	Country of origin
60/carton	12.24 kg	0.18 kg	0.11 kg	450x290x330 mm	200x100x30 mm	55x127x17 mm	China

DisplayPort™ and the DisplayPort™ logo are trademarks owned by the Video Electronics Standards Association (VESA®) in the United States and other countries.

The terms HDMI® and HDMI® High-Definition Multimedia Interface, and the HDMI® logo are trademarks or registered trademarks of HDMI® LA, Inc. in the United States and other countries.

Thunderbolt and the Thunderbolt logo are trademarks of Intel Corporation in the U.S. and/or other countries.

Apple and macOS, MAC, iTunes and Macintosh are registered trademarks of Apple Computer Inc.

Microsoft, Windows and the Windows logo are registered trademarks of Microsoft Corporation.

USB Type-C® and USB-C® are registered trademarks of USB Implementers Forum.

Chrome OS is a trademark of Google Inc. Use of this trademark is subject to Google Permissions.

All other trademarks and brand names are the property of their respective owners.

**For support please contact us via: [support@raidsonic.de](mailto:support@raidsonic.de)**  
**For orders please contact us via: [info@raidsonic.de](mailto:info@raidsonic.de)**