

MTS SPORTY RANGE

MTS Store - regular width

MTS Store - XXL width

S1PS SR FO HI CI ESD



DESCRIPTION

Based in southwest France since the company was founded in 1955, ANNIC SAS, better known as MTS More Than Safety is today one of Europe's foremost safety Footwear brands under the Honeywell portfolio. A sports line designed exclusively by MTS: the unique design and colours of MTS sporty range models combine aesthetics research, ergonomics and technological efficiency. As a result: a high-performance look and hightech materials, inspired by high-level sports. MTS Store S1P is a non-metallic safety shoe with a composite toe and an SR rated slip resistant rubber outsole. Made in France and manufactured according to ISO 9001.



MTS Store

FEATURES

- Suitable for Indoor/Outdoor use
- Ideal for: Logistics, Services, Warehouses and Transportation industries
- Composite toe cap protects against impact and compression
- Flexible and lightweight non metallic safety shoe, casual sporty design
- TPU heel counter for increased support, flexibility and comfort
- ESD marking
- Accessory: two types of insoles certified according to DGUV 112-191 : covers the user of orthopedic insoles in the workplace. When fitted with VAUPEL orthopedic insoles, has been tested and certified to continue to meet the requirements of the standard
- Accessory: modular three width Insock Fitting System: standard, wide or narrow – increases the comfort from wearing the shoe
- Available in regular width and in XXL width



Antistatic properties



Anti-puncture resistance
with PS level



Heel energy absorption



Cleated outsole SR:
Excellent Slip Resistance



Resistance to fuel oil



Heat Insulated Sole,
Cold Insulated Sole.



ESD: Certification of
Electrical resistance

TECHNICAL SPECIFICATIONS

Upper	Ondura Ozone (Black) with onSuede 1.7 mm
Lining	Orange colour full Artico lining and Black on MICRO Suede on heel counter
Fastening	Round tubular lace, Black color
Toe Cap	Toe cap resistant to an impact of 200 Joules, Composite Toe Cap
Midsole	Anti-perforation, non-metallic onPROTECTOR DIAMOND, type PS
Insock	Thermoformed PU foam, anatomic, antistatic, TITAN
Sole	Made from a combination of polyurethane (PU-PU), oil resistant FO, antistatic, ESD
Sole pattern	Multi-purpose, slip resistance conforms to SR standard
Weight (per one shoe)	Approximately 650 g
Colors	Black Orange
Sizes	35-50 (3-15UK)
Standard	EN ISO 20345:2022, S1PS SR FO HI CI ESD
Style	Low-cut

ORDERING INFORMATION

DESCRIPTION	REF. IN SAP	REF. IN ECHINOPS	SIZE
MTS Store - regular width	6270618	4585203	35-50
MTS Store - XXL width	6270624	4585803	35-50

MTS BY HONEYWELL SAFETY PRODUCTS UNITED KINGDOM

Honeywell House, Skimped Hill Lane,
Bracknell, Berkshire RG12 1EB
Phone: +44 (0) 1256 274938
Email: info-uk.hsp@honeywell.com

ANNIC S.A.S.

1 rue des usines
82250 laguepie – france
tel.: +33 (0) 563 302 101
fax.: +33 (0) 563 314 018
e-mail : contact@mts-morethansafety.com

MTS BY HONEYWELL SAFETY PRODUCTS NORDIC AB

Box 15 147
SE-167 15 Bromma – Sverige
Phone: +46 (0) 424480433
Email: info-nordic.hsp@honeywell.com

For More Information

sps.honeywell.com

For Information on Innovations and Patents

hsmpats.com

MTS BY HONEYWELL SAFETY PRODUCTS BENELUX BV

Lange Amerikaweg 55
7332 BP Apeldoorn, Nederland
Tel: +31 (0) 20 5656 988
Email: info-benelux.hsp@honeywell.com

