# Disclaimer. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Plain door, PrismaSeT HD, for electrical enclosure H2000 W300mm, RAL9003

NSYSFND203ED

! Launching in: 21 March 2024



### Main

Range	PrismaSeT	
Offer type	Spare part	
Accessory / separate part category	Enclosure accessory	
Product or component type	Door	
Application	Low voltage electrical distribution	
For enclosure nominal dimensions	- H: 2000 mm W: 300 mm	
Mounting location	Front	
Range compatibility	PrismaSeT PrismaSeT HD	
Device composition	1 door 1 lock with handle and 5 mm double bar insert 1 locking bar system 4 points 4 hinges 4 locking bar catches	
Quantity per set	Set of 1	

# Complementary

Material	Door: sheet steel	
Colour	White (RAL 9003)	
Surface finish	Epoxy-polyester powder	
Lock type	Lock 5 mm double bar	
Number of locks	1	
Door type	External plain	
Door opening side	Reversible (120 °)	
Height	Nominal: 1966 mm	
Width	Nominal: 269 mm	

### **Environment**

IK degree of protection IK10

# **Packing Units**

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	210.000 cm

Package 1 Width	29.000 cm
Package 1 Length	6.000 cm
Package 1 Weight	14.000 kg
Unit Type of Package 2	PAL
Number of Units in Package 2	18
Package 2 Height	47.000 cm
Package 2 Width	210.000 cm
Package 2 Length	120.000 cm
Package 2 Weight	284.000 kg

# **Contractual warranty**

Coverage	Core product
Warranty	18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

### Environmental Data explained >

How we assess product sustainability

Q	Environmental footprint
---	-------------------------

Environmental Disclosure

Product Environmental Profile

### **Use Better**

Materials and Substances	
Packaging made with recycled cardboard	No
Packaging without single use plastic	No
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
REACh Regulation	REACh Declaration

### **Use Again**

○ Repack and remanufacture	
Circularity Profile	No need of specific recycling operations
Take-back	No

# **Product datasheet**

# NSYSFND203ED

**Technical Illustration** 

**Exploded view** 



Image of product in real life situation

