



1/2"

1990

EXTENSION 1/2"

- Acc. to DIN 3123, ISO 3316
- For hand-operated sockets with square drive as per DIN 3120, ISO 1174, with ball locking device
- GEDORE vanadium steel 31CrV3, chrome-plated

12,5
1/2"





Code	No.	*	■"	■	↳mm↳	↳	↳	£
6143510	1990-2.1/2	*	1/2	12.5	63	115	10	
6143780	1990-3		1/2	12.5	76	137	10	
6143860	1990-5		1/2	12.5	125	188	10	
6142890	1990-7	*	1/2	12.5	180	264	10	
6143940	1990-10		1/2	12.5	250	361	10	
6129950	1990-12	*	1/2	12.5	305	411	10	

1990 A


EXTENSION 1/2" with release

- Easy access to deep-fitting screws
- Locking ring prevents unintentional release of the socket
- For hand-operated sockets with square drive as per DIN 3120, ISO 1174, with ball locking device

12,5
1/2"



Code	No.	■"	■	↳mm↳	↳	↳	£
1640828	1990 A-5	1/2	12.5	125	216	10	
1640801	1990 A-10	1/2	12.5	250	386	1	





1990 KR

UNIVERSAL EXTENSION 1/2"

- With ball end
- For hand-operated sockets with square drive as per DIN 3120, ISO 1174, with ball locking device
- The extension is able to pivot up to 15°
- Load capacity max. 230 N·m
- GEDORE vanadium steel 31CrV3, polished, chrome-plated

12,5
1/2"



Code	No.	■"	■	↳mm↳	↳	↳	£
6173180	1990 KR-5	1/2	12.5	125	180	10	
6225590	1990 KR-7	1/2	12.5	180	255	10	
6366570	1990 KR-10	1/2	12.5	250	345	10	

1994

COUPLER 1/2"

- Acc. to DIN 3122, ISO 3315
- For hand-operated sockets with square drive as per DIN 3120, ISO 1174, with ball locking device
- GEDORE vanadium steel 31CrV3, chrome-plated, polished

12,5
1/2"



Code	No.	■"	■	↳mm↳	↳	↳	£
6144670	1994	1/2	12.5	37.8	45	10	

1995

UNIVERSAL JOINT 1/2"

- Acc. to DIN 3123, ISO 3316
- For hand-operated sockets with square drive as per DIN 3120, ISO 1174, with ball locking device
- GEDORE vanadium steel 31CrV3, chrome-plated, polished

12,5
1/2"



Code	No.	■"	■	□"	□	↳mm↳	↳	↳	£
6144750	1995	1/2	12.5	1/2	12.5	72	159	10	

1996 - 1997

SWIVEL HANDLE 1/2"

- Acc. to DIN 3122, ISO 3315
- For hand-operated sockets with square drive as per DIN 3120, ISO 1174, with ball locking device
- GEDORE vanadium steel 31CrV3, chrome-plated, polished

12,5
1/2"



1996



1997

Code	No.	■"	■	↳mm↳	↳	↳	£
6144830	1996	1/2	12.5	255	426	10	
6144910	1997	1/2	12.5	381	593	10	