

## Features

- SATA Data
- SATA v2.0
- 3Gbp/s
- Black
- 45cm

## RS PRO 0.45m Locking SATA v2 Data Cable - Straight to Straight

RS Stock No. 0839407



RS Professionally Approved Products bring to you, professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

**Product Description**

*Internal Serial ATA data cable with 7 pin female data locking connectors. They are rated at SATA Revision 2.0 with speeds up to 3Gb/s.*

**General Specifications**


|                       |           |
|-----------------------|-----------|
| Connector A           | SATA Data |
| Connector A Style     | Straight  |
| Connector B           | SATA Data |
| Connector B Style     | Straight  |
| Length                | 45cm      |
| Outer Sheath Material | PVC       |
| Sheath Colour         | Black     |
| SATA Version          | v2.0      |
| Data Rate             | 3 Gbp/s   |

**Approvals**

|               |                    |
|---------------|--------------------|
| Standards Met | CE UKCA ROHS REACH |
|---------------|--------------------|

**Similar Products**

| Stock No.    | Brand  | Product Name                                                |
|--------------|--------|-------------------------------------------------------------|
| 0839407      | RS PRO | 0.45m Locking SATA v2 Data Cable - Straight to Straight     |
| NLRB-302LOCK | RS PRO | 0.45m Locking SATA v2 Data Cable - Straight to Straight     |
| NLRB-303LOCK | RS PRO | 0.45m Locking SATA v2 Data Cable - Right Angled             |
| NLRB-304LOCK | RS PRO | 0.45m Locking SATA v2 Data Cable - Straight to Right Angled |
| 0839406      | RS PRO | 0.45m Locking SATA v3 Data Cable - Straight to Straight     |
| 0839409      | RS PRO | 0.9m Locking SATA v2 Data Cable - Straight to Straight      |
| NLRB-307LOCK | RS PRO | 0.9m Locking SATA v2 Data Cable - Straight to Straight      |
| NLRB-308LOCK | RS PRO | 0.9m Locking SATA v2 Data Cable - Right Angled              |
| NLRB-309LOCK | RS PRO | 0.9m Locking SATA v2 Data Cable - Straight to Right Angled  |
| 0839408      | RS PRO | 0.9m Locking SATA v3 Data Cable - Straight to Straight      |



NOTE:

CABLE: 26AWG,UL2725,AL-FOIL,(26AWG\*2C+AL)\*2C+4D(28AWG),OD=5.0mm,BLACK COLOR,PVC JACKET.

CONNECTORS: SERIAL ATA 7P\*2PCS(BLACK INSULATOR,With Latch)

MOLD: MOLDING TYPE.

CONTACTS:

|               |       |   |   |   |   |
|---------------|-------|---|---|---|---|
| SERIAL ATA 7P | 1+4+7 | 2 | 3 | 5 | 6 |
| SERIAL ATA 7P | 1+4+7 | 2 | 3 | 5 | 6 |

OPEN/SHORT TEST: 100% TEST.

INSULATION: MIN. 2M.