



Datasheet

RS PRO HCK-BX Series 400V 3-Phase Box Fan Heaters

Stock number: 144-4362, 144-4363, 144-4364, 144-4365, 144-4366, 144-4367

EN

The RS Pro HCK-BX series is a range of heavy duty industrially styled electric box fan heaters. Available as either 1-Phase 240V and 3-Phase 400V models the HCK-BX series encompasses heat outputs from 2kW up to 22kW. Each model in the range has a stainless-steel heating element, metal fan blades, selectable heat output levels and adjustable thermostats for high efficiency. Each model in the HCK-BX series also features a quality powder coated steel case with either an insulated ergonomic carrying handle or combined support legs and carrying handles making them ideal for use in workshops, garages, greenhouses and building sites. The smaller 1-Phase and 3-Phase models are supplied with an integrated power cord fitted with either a UK plug or 3-Phase 16A 5 pin connector. The larger 3-Phase 400V models are equipped with a 400V 3-Phase 5 pin socket on the unit and require a separate 3-Phase power cable of the correct rating and type (not supplied).



HCK-BX15 (2019 Model)



HCK-BX22



HCK-BX9 (2019 Model)



HCK-BX5 (2019 Model)



HCK-BX2UK



HCK-BX3UK

For further details on the power cable requirements for the larger 400V models please see the following product specification table.

Internal

rspro.com

RS Pro HCK-BX Series Product Specifications

Model	RS Product Code	Description	Electrical Supply	Power Cord Specifications	Heat Output	Dimensions	Weight
HCK-BX2UK	144-4362	2kW Box Fan Heater	1-Phase 240V 13A 50Hz	13 amp UK Plug (FITTED)	1kW/2kW	235 x 225 x 330mm	3.5kg
HCK-BX3UK	144-4363	3kW Box Fan Heater	1-Phase 240V 13A 50Hz	13 amp UK Plug (FITTED)	1.5kW/3kW	270 x 255 x 400mm	4.6kg
HCK-BX5	144-4364	5kW Box Fan Heater	3-Phase 400V 16A 50Hz	16A 3-Phase 5 pin (FITTED)	2.5kW/5kW	270 x 255 x 400 mm	5.6kg
HCK-BX9	144-4365	9 kW Box Fan Heater	3-Phase 400V 16A 50Hz	16A 3-Phase 5 pin connector and cable (NOT SUPPLIED)	4.5kW/9kW	355 x 300 x 490mm	9.6kg
HCK-BX15	144-4366	15kW Box Fan Heater	3-Phase 400V 32A 50Hz	32A 3-Phase 5 pin connector and cable (NOT SUPPLIED)	5kW/10kW/15kW	410 x 360 x 550 mm	14.5kg
HCK-BX22	144-4367	22kW Box Fan Heater	3-Phase 400V 32A 50Hz	32A 3-Phase 5 pin lead and cable (SUPPLIED)	11kW/22kW	450 x 410 x 600mm	21.8kg