

PRODUCT-DETAILS

## AMD111520-AG

AMD111520-AG Switch 1-gang, 2-way, SP 20AX,  
Std rocker size - AG



### General Information

|                       |  |
|-----------------------|--|
| Extended Product Type | AMD111520-AG   |
| Product ID            | 2CLA610210N1656  |
| EAN                   | 8427238101200  |
| Catalog Description   | AMD111520-AG Switch 1-gang, 2-way, SP 20AX, Std rocker size - AG |
| Long Description      | Rated voltage: 250Vac<br>Rated current: 20AX                     |

### Ordering

|                        |               |
|------------------------|---------------|
| EAN                    | 8427238101200 |
| Customs Tariff Number  | 85365080      |
| Minimum Order Quantity | 10 piece      |

### Dimensions

|                            |          |
|----------------------------|----------|
| Product Net Depth / Length | 0.165 m  |
| Product Net Height         | 0.06 m   |
| Product Net Width          | 0.1 m    |
| Product Net Weight         | 0.029 kg |

### Container Information

|                                |               |
|--------------------------------|---------------|
| Package Level 1 Units          | 10 piece      |
| Package Level 1 EAN            | 8427238101200 |
| Package Level 1 Depth / Length | 0.165 m       |
| Package Level 1 Height         | 0.06 m        |
| Package Level 1 Width          | 0.1 m         |
| Package Level 1 Gross Weight   | 0.29 kg       |

## Technical

|                         |  |
|-------------------------|--|
| Ambient Air Temperature | Operation -5 ... +35 °C<br>Storage -5 ... +50 °C |
| Degree of Protection    | IP20   |
| Mounting Type           | Flush mounted (plaster)                          |

## Certificates and Declarations (Document Number)

|                                   |                       |
|-----------------------------------|-----------------------|
| Data Sheet, Technical Information | 9AKK106930A7740       |
| Declaration of Conformity - CE    | No declaration needed |
| Instructions and Manuals          | 9AKK106930A7740       |

## Classifications

|               |  |
|---------------|--|
| ETIM 7        | EC001590 - Switch  |
| ETIM 8        | EC001590 - Installation switch                             |
| WEEE Category | 5. Small Equipment (No External Dimension More Than 50 cm) |

## Categories

Low Voltage Products and Systems → Switch Assortments → Flush Mounted Range BS - Niessen → Design Millenium → Flush Mounted Inserts with Cover Plate → Mechanical Switch / Push Button

Low Voltage Products and Systems → Switch Assortments → Light / LoadControl → Mechanical Switch / Push Button → Mechanical Switch / Push Button - Flush Mounted → Mechanical Switch / Push Button

