




**Part Number :** [521160243](#)  
**Product Description :** Mizu-P25 5.00mm Pitch  
Waterproof Wire-to-Wire Plug Housing for  
AVSS 0.3, 2 Circuits, White  
**Series Number :** [52116](#)  
**Status :** Active  
**Product Category :** [Connector Housings](#)



## Documents & Resources


**Drawings**  
[521160243\\_sd.pdf](#)

**3D Models and Design Files**  
[521160243\\_stp.zip](#)

**Specifications**  
[AS-52117-001-001.pdf](#)  
[AS-52117-001-JP-001.pdf](#)  
[521160000-P00.pdf](#)  
[PS-52116-001-001.pdf](#)

## Product Environment Compliance

### Compliance

GADSL/IMDS	Compliant
China RoHS	
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant per EU 2015/863

### Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

### Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

## EU RoHS Certificate of Compliance

---

### Part Details

#### General

Status	Active
Category	Connector Housings
Series	52116
Description	Mizu-P25 5.00mm Pitch Waterproof Wire-to-Wire Plug Housing for AVSS 0.3, 2 Circuits, White
Application	Signal, Wire-to-Wire
Product Name	Mizu-P25 Waterproof,Splash Proof
UPC	883906527471

#### Agency

UL	E29179
----	--------

#### Physical

Circuits (maximum)	2
Color - Resin	White
Gender	Plug
Glow-Wire Capable	No
Lock to Mating Part	Yes
Material - Resin	Polyester
Net Weight	1.518/g
Number of Rows	1
Packaging Type	Tray
Panel Mount	No
Pitch - Mating Interface	5.00mm
Stackable	No
Temperature Range - Operating	-40° to +105°C

Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

---

Mates With / Use With

Mates with Part(s)

Description	Part Number
Mizu-P25 Waterproof Receptacle Housings	<u>52117</u>

Use with Part(s)

Description	Part Number
Mizu-P25 Male Crimp Terminals	<u>50038</u>

---

Application Tooling

Global

Description	Part Number
Sealing Cap Hand Tool	<u>622024400</u>