

Sapphire Iron

High cut resistant pu coated glove with steel fibre

Outstanding cut resistance allowing protection in the most risky applications. PU coating protects the hand from abrasion and grease, delivering effective long lasting grip.

Features

- ▲ Cut resistant: Level F / A6
- ▲ A flexible and comfortable glove offering great dexterity
- ▲ HPPE on the inside provides comfort and protection
- ▲ Steel is fully encapsulated with nylon on the outside to strengthen the protection against burns and sharp edges
- ▲ PU coating gives exceptional abrasion resistance and sensitivity allowing workers to handle small pieces
- ▲ Contact heat protection up to 100°C / 212°F for a short period (15 seconds max)
- ▲ Seamless knit prevents irritation
- ▲ Designed for easy movement and continuous wear

Certifications



Suitable industries & applications

Industries

- ▲ Automotive
- ▲ Construction
- ▲ Manufacturing
- ▲ Facilities Management
- ▲ Utilities
- ▲ Highways and Infrastructure
- ▲ Steel and Metals

Applications

- ▲ Machinery and Plant Operation
- ▲ Component and Product Assembly
- ▲ Vehicle Repairs and Maintenance
- ▲ Metal Fabrication Work
- ▲ Handling Sharp or Abrasive Materials

Europe

sales@globus.com
+44 (0)161 877 4747
+44 (0)161 877 4746

Middle East & Africa

sales.gcc@globusgroup.com
+971 4 882 9962
+971 4 882 9963

Americas

salesusa@globusgroup.com
+1 83 337 54747

Sapphire Iron

High cut resistant pu coated glove with steel fibre

Product information

Materials	Liner:	13 Gauge Engineered HPPE, Steel Fibre, Nylon, HPPE
	Coating:	Polyurethane
Colour	Grey / Black	
Length	280mm	
Cuff Style	Elasticated Knit Wrist	

Ordering information

XS	SKG00085FB	Items per Pack 10 x Pairs
S	SKG00085FD	
M	SKG00085FF	Items per Case 120 x Pairs
L	SKG00085FH	
XL	SKG00085FJ	
XXL	SKG00085FL	


Additional information

Certification legend



or click [here](#)

Declaration of conformity



or click [here](#)

View product online



or click [here](#)

Europe

sales@globus.com
+44 (0)161 877 4747
+44 (0)161 877 4746

Middle East & Africa

sales.gcc@globusgroup.com
+971 4 882 9962
+971 4 882 9963

Americas

salesusa@globusgroup.com
+1 83 337 54747

Globus Group, T2 Trafford Point, Twining Road, Trafford Park, Manchester, M17 1SH, UNITED KINGDOM
Globus EMEA FZE, Jafza One, Tower A, Office 2201, Jebel Ali, PO Box 61195, Dubai, UNITED ARAB EMIRATES
Globus Americas LLC, 45 Rockefeller Plaza, Suite 2000, New York City, New York, 10111, USA

The descriptions, characteristics, applications and photos are given for information purposes and do not constitute a contractual commitment.
The manufacturer reserves the right to make any modifications it deems necessary.