

Features

- ESD – Designed to safely discharge static electricity and protect electronic components from electrostatic discharge events.
- Wheeled
- Height Adjustable
- Available in different sizes

RS PRO ESD Stool

RS Stock No.: 0665649



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

Antistatic Stool is an excellent choice for environments where electrostatic control is essential. Made with high-quality dissipative fabric, it combines functionality with user comfort, offering long-lasting support and durability in demanding conditions. Perfect for workplaces where ESD control and reliability are top priorities.

Product Features:

- ✓ **Soft seat covered with dissipative fabric** – provides comfort during extended use and allows easy height adjustment for optimal support
- ✓ **Durable five-star chrome-plated steel base** – ensures stability and long-term resistance to intensive use
- ✓ **Resilient, easy-to-clean upholstery** – the high-quality fabric resists wear and stains, maintaining both appearance and function
- ✓ **Conductive castors** – rubber-coated to prevent floor damage and support ESD safety

An ideal solution for production and service environments that require both comfort and dependable electrostatic protection. Widely used across industries such as electronics, automotive, general manufacturing, medical, pharmaceutical, and defense.

General Specifications

TOTAL HEIGHT (mm)	535-715
TOTAL WIDTH (mm)	640
WEIGHT (kg)	8,7
MAX LOAD CAPACITY (kg)	120 (up to 200 kg with a special gas lift)
HEIGHT ADJUSTMENT RANGE (mm)	535-715mm
SEAT DIMENSIONS (mm)	355
ESD	YES
COLOUR	BLACK
MATERIAL	STANDARD
BASE MATERIAL	CHROME-PLATED STEEL
CASTORS	CONDUCTIVE, RUBBER-COATED TO PREVENT SCRATCHING
RESISTANCE GROUNDING (0hm)	10 ⁶ – 10 ⁸

Approvals

Chair compliance with standards	PN-EN IEC 61340-5-1:2025-02, PN-EN 1335-1:2004, PN-EN 1335-2:2009, PN-EN 1335-3:2009, PN-EN 1022:2007
Fabric compliance with standards	PN-EN 1021-1:2014-12, PN-EN 1021-2:2014-12

Similar Products

Stock No.	Brand	Product Name
0665645	RS PRO	ESD PU Stool chair, seat height adjustment 430-555mm
0665646	RS PRO	ESD PU Stool chair, seat height adjustment 515-700mm
0665647	RS PRO	ESD PU Stool chair, seat height adjustment 560-810mm
0665642	RS PRO	ESD PU Stool chair, seat height adjustment 430-555mm
0665643	RS PRO	ESD PU Stool chair, seat height adjustment 510-695mm
0665644	RS PRO	ESD PU Stool chair, seat height adjustment 560-810mm
0665648	RS PRO	ESD Stool chair, seat height adjustment 455-575mm
0665650	RS PRO	ESD Stool chair, seat height adjustment 585-835mm

Accessories

Stock No.	Brand	Product Name
0665661	RS PRO	ESD castor, grey rubber tyre, diameter 50mm (**brake option available on request**)
0665662	RS PRO	ESD metal castor, diameter 50mm
0665664	RS PRO	ESD glides
0665665	RS PRO	ESD footrest