

WP-GR HF IP66 PG11 BK - Protective hose screw connection



3240946

<https://www.phoenixcontact.com/gb/products/3240946>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cable gland, Pg thread, IP66 protection, with strain relief

Commercial data

Item number	3240946
Packing unit	20 pc
Minimum order quantity	20 pc
Sales key	AF7DSA
Product key	AF7DSA
Catalog page	Page 590 (C-3-2019)
GTIN	4046356710534
Weight per piece (including packing)	14.175 g
Weight per piece (excluding packing)	14.175 g
Customs tariff number	39174000
Country of origin	DE

WP-GR HF IP66 PG11 BK - Protective hose screw connection



3240946

<https://www.phoenixcontact.com/gb/products/3240946>

Technical data

Product properties

Product type	Protective hose screw connection
Application	Cable gland
Type of the screw connection	Conduit adapter
Type	Outer thread
Cable outlet	straight
Thread type	Pg

Dimensions

Width	23 mm
Height	59 mm
Wrench size	21 mm
Wrench size for mounting	21 mm
	22 mm

External dimensions

Outside diameter	12 mm
------------------	-------

Material specifications

Material	PA 6
Flammability rating according to UL 94	V2
Material for screw connection	PA
Components	free from silicone, halogen, and cadmium

Cable/line

Halogen-free	yes
--------------	-----

Mechanical properties

Mechanical data

Type of the screw connection	Conduit adapter
------------------------------	-----------------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP66
Ambient temperature (operation)	-40 °C ... 120 °C

WP-GR HF IP66 PG11 BK - Protective hose screw connection



3240946

<https://www.phoenixcontact.com/gb/products/3240946>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/3240946>



UL Recognized
Approval ID: E86359



LR



VDE approval of drawings

WP-GR HF IP66 PG11 BK - Protective hose screw connection



3240946
<https://www.phoenixcontact.com/gb/products/3240946>

Classifications

ECLASS

ECLASS-13.0	27430311
-------------	----------

ETIM

ETIM 9.0	EC001178
----------	----------

UNSPSC

UNSPSC 21.0	39121300
-------------	----------

WP-GR HF IP66 PG11 BK - Protective hose screw connection



3240946
<https://www.phoenixcontact.com/gb/products/3240946>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk