


PRODUCT SPECIFICATION

**Carl
Kammerling**
International

Brand	C.K
Product Range	Soldering Irons
Catalogue number	950
Date	12/04/2012

<p>Range Description Soldering Irons</p> <p>Features</p> <ul style="list-style-type: none"> • Heavy duty construction – for professional use • GS & VDE approved – independently certified • Long life tip – suitable for use with lead free solder • Support stand included 	
--	--

Item Number	Item Description	EAN No	Commodity code	Carton Qty
495009	25w Soldering Iron UK	505107495009	85151100	1
495010	40w soldering Iron UK	505107495010	85151100	1
495011	25w Soldering Iron Euro	505107495011	85151100	1
495012	40w Soldering Iron Euro	505107495012	85151100	1
495013	Spare tip 25w (Pack of 2)	505107495013	85151100	1
495014	Spare tip 40w (Pack of 2)	505107495014	85151100	1

Technical product information	<p>Materials Handle – Injection moulded thermo-setting polyurethane Heating element – Heater wire (chrome nickel steel) Shaft – Stainless steel Tip – Copper with nickel Iron plating</p> <p>25w Soldering Iron 25w output Voltage 220 – 240v AC Current 0.1 amp Fuse rating 3 amp Tip width 2.7mm</p> <p>40w Soldering Iron 40w output Voltage 220 – 240v AC Current 0.17 amp Fuse rating 3 amp Tip width 3.5mm</p>
Standards compliance	VDE approved product
User health and safety information	Users are directed to carefully read and observe the operating instructions
RoHS/WEEE compliance	<p>RoHS – these products are implicated within the scope of the legislation, Carl Kammerling International hold evidence of compliance, available on request</p> <p>Carl Kammerling International is a registered producer of RoHS compliant products</p> <p>WEEE - markings on C.K soldering Irons are compliant with WEEE directives</p>
Material safety data	None applicable
Warranty	C.K soldering irons are guaranteed for life against imperfect materials or workmanship
Country of origin	Germany

Dimensional details

Item	Product only				Product on primary packaging			
	Width mm	Depth mm	Height mm	Net weight g	Width mm	Depth mm	Height mm	Gross weight g
495009	45	45	1600	193	70	40	350	270
495010	45	45	1600	193	70	40	350	270
495011	45	45	1600	193	70	40	350	270
495012	45	45	1600	193	70	40	350	270

495013	4	4	65	5	80	6	145	22
495014	5	5	75	10	80	6	145	32

Item	Shelf box (secondary packaging)				Euro Pallet data Wi x Hi	
	Width mm	Depth mm	Height mm	Gross weight g	No of cartons on base	Number of rows high
495009						
495010						
495011						
495012						
495013						
495014						

Packaging waste details

Item	Primary Packaging				Secondary packaging			
	Plastic g	Use	Card g	Use	Plastic g	Use	Card g	Use
495009			77	Box				
495010			77	Box				
495011			77	Box				
495012			77	Box				
495013	2	Blister	10	Backing card				
495014	2	Blister	10	Backing card				