



129-108-4

**1/4"-1/2" Hex Socket Set Metric,
108 Pcs**






PRODUCT DETAILS

- 108 pcs socket set
- Hex sockets, metric sizes
- Chrome plated bright finish
- High density polyethylene box
- Box with metal latches
- Contents, 108 pcs
- DIN 3120, DIN 3124, DIN 3122, ISO 10102



PRODUCT ATTRIBUTES

Product			
129-108-4	108	80 x 280 x 380 mm	7100 g

SET CONTENT



Hex Key Nickel Plated 1.5 mm
040001



Hex Key Nickel Plated 2 mm - 5/64"
040011



Hex Key Nickel Plated 2.5 mm
040021



Socket 1/4" Hex 4 mm
101-04-1



Socket 1/4" Hex 4.5 mm
101-045-1



Socket 1/4" Hex 5 mm
101-05-1



Socket 1/4" Hex 5.5 mm
101-055-1



Socket 1/4" Hex 6 mm
101-06-1



Socket 1/4" Hex 7 mm
101-07-1



Socket 1/4" Hex 8 mm
101-08-1



Socket 1/4" Hex 9 mm
101-09-1



Socket 1/4" Hex 10 mm
101-10-1



Socket 1/4" Hex 11 mm
101-11-1



Socket 1/4" Hex 12 mm
101-12-1



Socket 1/4" Hex 13 mm
101-13-1



Socket 1/4" Hex 14 mm
101-14-1



Socket 1/4" Deep Hex 6 mm
103-06-1



Socket 1/4" Deep Hex 7 mm
103-07-1



Socket 1/4" Deep Hex 8 mm
103-08-1



Socket 1/4" Deep Hex 9 mm
103-09-1



Socket 1/4" Deep Hex 10 mm
103-10-1



Socket 1/4" Deep Hex 11 mm
103-11-1



Socket 1/4" Deep Hex 12 mm
103-12-1



Socket 1/4" Deep Hex 13 mm
103-13-1



Extension 1/4" 50 mm
105-22-1



Extension 1/4" 100 mm
105-24-1



Universal Joint 1/4"
105-40-1



Sliding T-Handle 1/4"
105-42-1



Spinner Handle 1/4"
105-50-1



Ratchet 1/4" Pear Type, 72 Teeth,
150 mm
105-70-1



Socket 1/4" Torx E-4
106-04-1



Socket 1/4" Torx E-5
106-05-1



Socket 1/4" Torx E-6
106-06-1



Socket 1/4" Torx E-7
106-07-1



Socket 1/4" Torx E-8
106-08-1



Hex Bit Socket 1/4" 3 mm
107-H3-1



Hex Bit Socket 1/4" 4 mm
107-H4-1



Hex Bit Socket 1/4" 5 mm
107-H5-1



Hex Bit Socket 1/4" 6 mm
107-H6-1



Phillips Bit Socket 1/4" PH1
107-PH1-1



Phillips Bit Socket 1/4" PH2
107-PH2-1



Pozidriv Bit Socket 1/4" PZ1
107-PZ1-1



Pozidriv Bit Socket 1/4" PZ2
107-PZ2-1



Torx Bit Socket 1/4" T8
107-T08-1



Torx Bit Socket 1/4" T10
107-T10-1



Torx Bit Socket 1/4" T15
107-T15-1



Torx Bit Socket 1/4\" T20
107-T20-1



Torx Bit Socket 1/4\" T25
107-T25-1



Torx Bit Socket 1/4\" T27
107-T27-1



Torx Bit Socket 1/4\" T30
107-T30-1



Slotted Bit Socket 1/4\" 0.8x4
107-0840-1



Slotted Bit Socket 1/4\" 1x5.5
107-1055-1



Slotted Bit Socket 1/4\" 1.2x8
107-1280-1



Socket 1/2\" Deep Bihex 14 mm
124-14-1



Socket 1/2\" Deep Bihex 15 mm
124-15-1



Socket 1/2\" Deep Bihex 17 mm
124-17-1



Socket 1/2\" Deep Bihex 19 mm
124-19-1



Socket 1/2\" Deep Bihex 22 mm
124-22-1



Extension 1/2\" 125 mm
125-23-1



Extension 1/2\" 250 mm
125-25-1



Universal Joint 1/2\"
125-40-1



Sliding T-Handle Head 1/2\"
125-43-1



Bit Holder 1/2" to Hex 5/16"
125-48-1



Spark Plug 1/2" Size 5/8"
125-53-1



Spark Plug 1/2" Size 13/16"
125-54-1



**Ratchet 1/2" Pear Type, 72 Teeth,
250 mm**
125-70-1



5/16" Bit Hex 10, 2 Pcs
470-H10-1



5/16" Bit Hex 7, 2 Pcs
470-H7-1



5/16" Bit Hex 8, 2 Pcs
470-H8-1



5/16" Bit PH3, 2 Pcs
470-PH3-1



5/16" Bit PH4, 2 Pcs
470-PH4-1



5/16" Bit Torx 40, 2 Pcs
470-T40-1



5/16" Bit Torx 45, 2 Pcs
470-T45-1



5/16" Bit Torx 50, 2 Pcs
470-T50-1



5/16" Bit Torx 55, 2 Pcs
470-T55-1



5/16" Bit Slotted 10, 2 Pcs
470-10.0-1



5/16" Bit Slotted 12, 2 Pcs
470-12.0-1



5/16" Bit Slotted 8.0, 2 Pcs
470-8.0-1



Socket 1/2" Torx E-10
126-10-1



Socket 1/2" Torx E-12
126-12-1



Socket 1/2" Torx E-16
126-16-1



Socket 1/2" Torx E-20
126-20-1



Socket 1/2" Hex 10 mm
121-10-1



Socket 1/2" Hex 12 mm
121-12-1



Socket 1/2" Hex 14 mm
121-14-1



Socket 1/2" Hex 16 mm
121-16-1



Socket 1/2" Torx E-11
126-11-1



Socket 1/2" Torx E-14
126-14-1



Socket 1/2" Torx E-18
126-18-1



Socket 1/2" Torx E-24
126-24-1



Socket 1/2" Hex 11 mm
121-11-1



Socket 1/2" Hex 13 mm
121-13-1



Socket 1/2" Hex 15 mm
121-15-1



Socket 1/2" Hex 17 mm
121-17-1



Socket 1/2" Hex 18 mm
121-18-1



Socket 1/2" Hex 19 mm
121-19-1



Socket 1/2" Hex 20 mm
121-20-1



Socket 1/2" Hex 21 mm
121-21-1



Socket 1/2" Hex 22 mm
121-22-1



Socket 1/2" Hex 24 mm
121-24-1



Socket 1/2" Hex 27 mm
121-27-1



Socket 1/2" Hex 30 mm
121-30-1



Socket 1/2" Hex 32 mm
121-32-1