


# Arteor™ RJ 45 sockets



Support frame and plate selection charts **p. 414-421**

With LCS<sup>2</sup> connector with fast connection thanks to integrated crimping  
 Take AWG 22 single-core cables up to AWG 26 and AWG multicore cables  
 Contacts marked with dual colour code and wiring schemes T568 A and T 568 B  
 Conform to standards ISO/IEC 11801 Ed. 2.0, amendment 2, EN 50173-1 and TIA/EIA 568 C  
 Mechanisms supplied with rocker plates, to be equipped with support frames (p. 411) and plates (p. 414 to 421)

Pack	Cat.Nos	Cat. 6A sockets
		360° metal shielding
	<b>NEW</b>	<b>STP - 1 module</b>
10	5 723 06	○ White
10	5 728 06	● Magnesium
10	5 723 51	○ White with orange shutter
10	5 728 51	● Magnesium with orange shutter
10	5 723 52	○ White with green shutter
10	5 728 52	● Magnesium with green shutter
		<b>STP with controlled access - 2 modules</b> Supplied with 2 keys for 5 sockets
5	5 723 50	○ White with red shutter
5	5 728 50	● Magnesium with red shutter
		<b>UTP - 1 module</b>
10	5 723 49	○ White
10	5 728 49	● Magnesium
10	5 723 59	○ White with green shutter
10	5 728 59	● Magnesium with green shutter
10	5 723 58	○ White with orange shutter
10	5 728 58	● Magnesium with orange shutter
		<b>UTP with controlled access - 2 modules</b> Supplied with 2 keys for 5 sockets
5	5 723 57	○ White with red shutter
5	5 728 57	● Magnesium with red shutter

Pack	Cat.Nos	Cat. 6 sockets
	<b>NEW</b>	<b>UTP - 1 module</b>
10	5 723 02	○ White
10	5 728 02	● Magnesium
10	5 723 54	○ White with orange shutter
10	5 728 54	● Magnesium with orange shutter
10	5 723 55	○ White with green shutter
10	5 728 55	● Magnesium with green shutter
		<b>UTP - 2 modules</b>
10	5 723 14	○ White - square version
10	5 728 14	● Magnesium - square version
10	5 723 24	○ White - round version
10	5 728 24	● Magnesium - round version

Pack	Cat.Nos	Cat. 6 sockets (continued)
	<b>NEW</b>	<b>UTP with controlled access - 2 modules</b> Supplied with 2 keys for 5 sockets
5	5 723 53	○ White with red shutter
5	5 728 53	● Magnesium with red shutter
		<b>UTP with retractable cord - 4 modules</b> Cord (0.9 m) winds up automatically with a pushbutton
1	5 723 39	○ White
1	5 728 39	● Magnesium
		<b>FTP - 1 module</b>
10	5 723 22	○ White
10	5 728 22	● Magnesium
		<b>FTP - 2 modules</b>
10	5 723 16	○ White
10	5 728 16	● Magnesium
		<b>STP shielded - 1 module</b>
10	5 723 23	○ White
10	5 728 23	● Magnesium
		<b>STP shielded - 2 modules</b>
10	5 723 17	○ White
10	5 728 17	● Magnesium

Pack	Cat.Nos	Cat. 5e sockets
	<b>NEW</b>	<b>UTP - 1 module</b>
10	5 723 03	○ White
10	5 728 03	● Magnesium
		<b>UTP - 2 modules</b>
10	5 723 15	○ White
10	5 728 15	● Magnesium
		<b>FTP - 1 module</b>
10	5 723 04	○ White
10	5 728 04	● Magnesium