

## Features

- ESD – Designed to safely discharge static electricity and protect electronic components from electrostatic discharge events.
- Height Adjustable
- Available in different sizes

## RS PRO ESD Stool

RS Stock No.: 0665648



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

Antistatic Stool is an excellent choice for environments where electrostatic control is essential. Made with high-quality dissipative fabric, it combines functionality with user comfort, offering long-lasting support and durability in demanding conditions. Perfect for workplaces where ESD control and reliability are top priorities.

### Product Features:

- ✓ **Soft seat covered with dissipative fabric** – provides comfort during extended use and allows easy height adjustment for optimal support
- ✓ **Durable five-star chrome-plated steel base** – ensures stability and long-term resistance to intensive use
- ✓ **Safety-First Design** – For maximum safety, the tallest model is equipped with glides instead of castors
- ✓ **Resilient, easy-to-clean upholstery** – the high-quality fabric resists wear and stains, maintaining both appearance and function

An ideal solution for production and service environments that require both comfort and dependable electrostatic protection. Widely used across industries such as electronics, automotive, general manufacturing, medical, pharmaceutical, and defense.

## General Specifications

|                              |                                            |
|------------------------------|--------------------------------------------|
| TOTAL HEIGHT (mm)            | 585-835                                    |
| TOTAL WIDTH (mm)             | 700                                        |
| WEIGHT (kg)                  | 9,2                                        |
| MAX LOAD CAPACITY (kg)       | 120 (up to 200 kg with a special gas lift) |
| HEIGHT ADJUSTMENT RANGE (mm) | 585-835mm                                  |
| SEAT DIMENSIONS (mm)         | 355                                        |
| ESD                          | YES                                        |
| COLOUR                       | BLACK                                      |
| MATERIAL                     | STANDARD                                   |
| BASE MATERIAL                | CHROME-PLATED STEEL                        |
| GLIDES                       | CONDUCTIVE                                 |
| RESISTANCE GROUNDING (0hm)   | $10^6 - 10^8$                              |

## Approvals

|                                         |                                                                                                       |
|-----------------------------------------|-------------------------------------------------------------------------------------------------------|
| <b>Chair compliance with standards</b>  | PN-EN IEC 61340-5-1:2025-02, PN-EN 1335-1:2004, PN-EN 1335-2:2009, PN-EN 1335-3:2009, PN-EN 1022:2007 |
| <b>Fabric compliance with standards</b> | PN-EN 1021-1:2014-12, PN-EN 1021-2:2014-12                                                            |

## Similar Products

| Stock No. | Brand  | Product Name                                         |
|-----------|--------|------------------------------------------------------|
| 0665645   | RS PRO | ESD PU Stool chair, seat height adjustment 430-555mm |
| 0665646   | RS PRO | ESD PU Stool chair, seat height adjustment 515-700mm |
| 0665647   | RS PRO | ESD PU Stool chair, seat height adjustment 560-810mm |
| 0665642   | RS PRO | ESD PU Stool chair, seat height adjustment 430-555mm |
| 0665643   | RS PRO | ESD PU Stool chair, seat height adjustment 510-695mm |
| 0665644   | RS PRO | ESD PU Stool chair, seat height adjustment 560-810mm |
| 0665648   | RS PRO | ESD Stool chair, seat height adjustment 455-575mm    |
| 0665649   | RS PRO | ESD Stool chair, seat height adjustment 535-715mm    |

## Accessories

| Stock No. | Brand  | Product Name                                                                        |
|-----------|--------|-------------------------------------------------------------------------------------|
| 0665661   | RS PRO | ESD castor, grey rubber tyre, diameter 50mm (**brake option available on request**) |
| 0665662   | RS PRO | ESD metal castor, diameter 50mm                                                     |
| 0665664   | RS PRO | ESD glides                                                                          |
| 0665665   | RS PRO | ESD footrest                                                                        |