

Base strip - FK-MPT 0,5/ 6-ICA-3,5 - 1930360

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Header, Nominal current: 3 A, Rated voltage (III/2): 250 V, Number of positions: 6, Pitch: 3.5 mm, Color: black, Contact surface: Tin, Mounting: Soldering, The touch-protected basic strip, serves to accommodate the FK-MPT 0,5 PCB terminal block.



The figure shows a 9-pos. version of the product

Why buy this product

- ✓ Also available without a side panel on request, e.g., where space is restricted
- ✓ Available in vertical and horizontal versions
- ✓ Easy pre-assembly
- ✓ 3.5 mm pitch
- ✓ With closed side panels
- ✓ Shock-proof base strip for FK-MPT PCB terminal block
- ✓ Protection against mismatching thanks to asymmetrical arrangement of sockets



Key commercial data

Packing unit	50 pc
Minimum order quantity	50 pc
GTIN	 4 017918 823184
Weight per Piece (excluding packing)	1.64 g
Custom tariff number	85366990
Country of origin	Germany
Note	Made to Order (non-returnable)

Technical data

Dimensions

Length	8.8 mm
Pitch	3.5 mm
Dimension a	17.5 mm
Pin dimensions	0,3 x 0,9 mm
Hole diameter	1 mm

Base strip - FK-MPT 0,5/ 6-ICA-3,5 - 1930360

Technical data

General

Range of articles	FK-MPT 0,5/...-ICA
Insulating material group	IIIa
Rated surge voltage (III/3)	2.5 kV
Rated surge voltage (III/2)	2.5 kV
Rated surge voltage (II/2)	2.5 kV
Rated voltage (III/3)	160 V
Rated voltage (III/2)	250 V
Rated voltage (II/2)	250 V
Connection in acc. with standard	EN-VDE
Nominal current I_N	3 A
Maximum load current	3 A
Insulating material	PA
Inflammability class according to UL 94	V0
Color	black
Number of positions	6

Classifications

eCl@ss

eCl@ss 4.0	272607xx
eCl@ss 4.1	27260701
eCl@ss 5.0	27260701
eCl@ss 5.1	27260701
eCl@ss 6.0	27260704
eCl@ss 7.0	27440402
eCl@ss 8.0	27440402

ETIM

ETIM 3.0	EC001121
ETIM 4.0	EC002637
ETIM 5.0	EC002637

UNSPSC

UNSPSC 6.01	30211801
UNSPSC 7.0901	39121432
UNSPSC 11	34131203
UNSPSC 12.01	39121432
UNSPSC 13.2	39121432

Approvals

Approvals

Base strip - FK-MPT 0,5/ 6-ICA-3,5 - 1930360

Approvals

Approvals

UL Recognized / cUL Recognized / EAC / cULus Recognized

Ex Approvals

Approvals submitted

Approval details

UL Recognized 		
	B	D
Nominal current I _N	4 A	4 A
Nominal voltage U _N	300 V	300 V

cUL Recognized 		
	B	D
Nominal current I _N	4 A	4 A
Nominal voltage U _N	300 V	300 V


EAC

cULus Recognized 
--

Drawings

Base strip - FK-MPT 0,5/ 6-ICA-3,5 - 1930360

Drilling diagram



Dimensioned drawing

