

M105

Soft foam tray with tool assortment

14" 38"

7,7 kg

	art.	
024500871	M105	
024510107	MV107	Tray M105, empty



- n. 13 **900**: 1/4" hexagon sockets ○ 4 - 4,5 - 5 - 5,5 - 6 - 7 - 8 - 9 - 10 - 11 - 12 - 13 - 14 mm
- n. 9 **900L**: hexagon hand sockets, long series ○ 5 - 6 - 7 - 8 - 9 - 10 - 11 - 12 - 13 mm
- n. 9 **96BPC/SC9**: ball head offset hexagon key wrenches ○ 1,5 - 2 - 2,5 - 3 - 4 - 5 - 6 - 8 - 10 mm
- n. 1 **895/1**: socket holder
- n. 1 **895/3**: socket holder
- n. 1 **895/6**: socket holder
- n. 5 **900ME**: 1/4" socket drivers for hexagon screws ○ 3-4-5-6-7 mm
- n. 4 **900LP**: 1/4" socket drivers for slotted head screws ● 0,8x4 - 1x5,5 - 1,2x6,5 - 1,2x8 mm
- n. 4 **900PH**: 1/4" socket drivers for cross head Phillips® screws ⚙ PH1-PH2-PH3-PH4
- n. 7 **900TX**: socket drivers for Torx® head screws ⚙ T10 - T15 - T20 - T25 - T27 - T30 - T40
- n. 1 **900/16**: adaptor, 1/4" female and 3/8" male drives □ 1/4 - ■ 3/8
- n. 3 **900/...**: 1/4" drive extension bar 50-100-150 mm
- n. 1 **900/25**: 1/4" drive universal joint
- n. 1 **900BG/30**: 1/4" drive spinner handle
- n. 1 **900/42**: 1/4" drive swivel T-handle
- n. 1 **900/55**: 1/4" reversible ratchet ⚙
- n. 17 **910A**: 3/8" hexagon hand sockets ○ 6 - 7 - 8 - 9 - 10 - 11 - 12 - 13 - 14 - 15 - 16 - 17 - 18 - 19 - 20 - 21 - 22 mm
- n. 1 **910/15**: adaptor, 3/8" female and 1/4" male drivers □ 3/8 - ■ 1/4
- n. 1 **910/16**: adaptor, 1/2" female and 3/8" male drives □ 3/8 - ■ 1/2
- n. 1 **910/21**: 3/8" extension bar 125 mm
- n. 1 **910/22**: 3/8" extension bar 250 mm
- n. 1 **910/25**: 3/8" drive universal joint
- n. 1 **910/42**: 3/8" drive sliding T - handle
- n. 1 **910/55**: 3/8" reversible ratchet ⚙
- n. 21 **920A**: 1/2" square drive hexagon sockets ○ 8 - 10 - 11 - 12 - 13 - 14 - 15 - 16 - 17 - 18 - 19 - 20 - 21 - 22 - 23 - 24 - 26 - 27 - 28 - 30 - 32 mm
- n. 1 **920/15**: adaptor, 1/2" female and 3/8" male drives □ 1/2 - ■ 3/8
- n. 1 **920/25**: 1/2" drive universal joint
- n. 2 **920AN**: 1/2" wobble extension bar 125 - 250 mm
- n. 1 **920/42**: 1/2" drive sliding T-handle
- n. 1 **920/55**: 1/2" reversible ratchet ⚙
- n. 3 **956E**: 3/8" square drive spark plug sockets ○ 16-17,8-20,8 mm