

3000 Apron with Sleeves - Model 243-G01

Durable, comfortable multi-layer chemical barrier

Durable material providing an effective barrier against a range of inorganic chemicals and biological agents..



Industries

- Chemical
- Mining
- Food Processing

Applications

- Unexpected leakages spills or other releases
- Loading and unloading trucks and vehicles
- Loading trucks & vehicles
- Product inspection
- Cleaning of plant and machines

KEY FEATURES & BENEFITS

- Protective multi-layer barrier fabric effective against numerous chemicals
- Highly visible bright yellow color for improved worker safety
- Attached Solvex® 37- 676 gloves
- Lightweight and durable

Technology



MICROCHEM™
Chemical Barrier Technology


Material Diagram




External film
barrier layer

Core high barrier
film layer

Non-woven
inner layer



Seam Diagram



Performance Standards


PARTIAL BODY
PROTECTION ONLY


TYPE PB [3]


TYPE PB [4]


EN 14126

EN ISO 13688:2013


TYPE PB [6]

Product Information

Product Information	
Available Sizes	S, M, L, XL, 2XL, 3XL
Color	Yellow
Packaging Overview	Individually packaged
Product Material	Multi-layer non-woven barrier Laminate fabric
Product Reference	3000 Apron with Sleeves - Model 243-G01
Standards Overview	CE CATEGORY III (Type PB [3]-B, Type PB [4]-B, Type PB [6]-B, EN 14126
Seam Type	Welded and Taped
Shelf Life	5 years
Style Number	Y30T243A

Suit components & accessories

Suit Components and Accessories	
Design Features	Apron with sleeves with rear velcro fastening at the neck and attached Solvex [®] 37-676 gloves.

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region
Ansell Healthcare Europe NV
T: +32 (0) 2 528 74 00

North America Region
Ansell Healthcare Products LLC
T: +1 800 800 0444

Australia
Ansell Limited
T: +61 1800 337 041

Asia Pacific Region
Ansell Global Trading Center
T: +603 8310 6688

Latin America & Caribbean Region
Ansell Commercial Mexico S.A. de C.V.
T: +52 442 248 1544 / 248 3133

Ansell, [®] and [™] are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

