



Reducing coupling

- installation without disassembling
- suitable for PE and PEX pipes
- water PN16
- material: PP
- gasket: NBR quality for drinkable water
- colour: blue-black

d (mm)	d-d (mm)	PN (bar)	Code	SP	GP	Weight (kg)
25	25 - 20	16	158 400 153	10	120	0.088
32	32 - 20	16	158 400 154	10	90	0.122
32	32 - 25	16	158 400 155	10	90	0.137
40	40 - 25	16	158 400 156	65	0	0.183
40	40 - 32	16	158 400 157	65	0	0.210
50	50 - 32	16	158 400 158	40	0	0.340
50	50 - 40	16	158 400 159	35	0	0.376
63	63 - 32	16	158 400 160	20	0	0.543
63	63 - 40	16	158 400 161	20	0	0.583
63	63 - 50	16	158 400 162	18	0	0.676
75	75 - 50	16	158 400 163	15	0	0.993
75	75 - 63	16	158 400 164	12	0	1.182
90	90 - 63	16	158 400 165	8	0	1.603
90	90 - 75	16	158 400 166	6	0	1.859
110	110 - 90	16	158 400 167	3	0	2.822

d (mm)	d-d (mm)	d1 (mm)	D (mm)	D1 (mm)	L (mm)	l1 (mm)	l2 (mm)	l3 (mm)	l4 (mm)
25	25 - 20	20	53	45	117	59	21	54	19
32	32 - 20	20	64	45	130	66	23	54	19
32	32 - 25	25	64	53	130	66	23	59	21
40	40 - 25	25	75	53	160	76	26	59	21
40	40 - 32	32	75	64	164	76	26	66	23
50	50 - 32	32	97	64	175	88	30	66	23
50	50 - 40	40	97	75	204	88	30	76	26
63	63 - 32	32	114	64	210	104	35	66	23
63	63 - 40	40	114	75	216	104	35	76	26
63	63 - 50	50	114	97	216	104	35	88	30
75	75 - 50	50	135	97	237	133	41	88	30
75	75 - 63	63	135	114	249	133	41	104	35
90	90 - 63	63	161	114	292	150	44	104	35
90	90 - 75	75	161	135	366	150	44	133	41
110	110 - 90	90	185	161	363	175	53	150	44

The technical data are not binding. They neither constitute expressly warranted characteristics nor guaranteed properties nor a guaranteed durability. They are subject to modification. Our General Terms of Sale apply.

Georg Fischer Piping Systems Ltd, Postfach, CH-8201 Schaffhausen/Switzerland
 Phone +41 -(0)52-631 1111
 e-mail: info.ps@georgfischer.com
 Internet: <http://www.gfps.com>