

Product data sheet

Specifications



Repacked, ceiling box, Multifix, with surface cover and lighting plug E27

IMT35023W



This repacked option saves 17.015 over the standard condition

Main

Range of product	Multifix
Product name	Multifix Air
Product or component type	Ceiling box
Device application	Airtight installation
Device presentation	With surface cover and lighting plug E27
Provided equipment	Lighting plug with E27 base Hook Surface cover IPX4 DCL outlet DCL plug 2P+E 6A/250 VAC Pre-mounted suspension chimney
Quantity per set	Set of 10

Complementary

Function available	Anti-rotation system
Number of gangs	1 gang
fixing mode	By screws
Material	PP (polypropylene)/TPE (thermoplastic elastomer) PC (polycarbonate)/ABS (acrylonitrile butadiene-styrene) PA (polyamide) 6.6 Steel ABS (acrylonitrile butadiene-styrene)
mechanical robustness	Airtight Fire resistance
Colour tint	Green (NCS S 2070-G80Y)
Cable entry	4 knock-out
drill diameter/depth	67 mm 50 mm
Height	71 mm
Width	71 mm
Depth	49 mm

Environment

Ambient air temperature for operation	-5...60 °C
IP degree of protection	IP20
fire resistance	850 °C
Standards	EN 60670-1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.500 cm
Package 1 Width	13.500 cm
Package 1 Length	14.000 cm
Package 1 Weight	107.000 g
Unit Type of Package 2	S02
Number of Units in Package 2	10
Package 2 Height	15.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	1.386 kg
Unit Type of Package 3	P06
Number of Units in Package 3	160
Package 3 Height	75.000 cm
Package 3 Width	60.000 cm
Package 3 Length	80.000 cm
Package 3 Weight	30.176 kg

Contractual warranty

Warranty (in months)	18
----------------------	----



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)



Environmental footprint

Lower carbon footprint

17 kg CO2 eq.

Use Better



Materials and Substances

EU RoHS Directive

[Compliant](#)

REACH Regulation

[Free of Substances of Very High Concern above the threshold](#)

Use Longer



Lifetime extension

Repair

No

Use Again



Repack and remanufacture

Take-back

No