

Features

- Proof load tested to $1.5 \times \text{WLL}$ for maximum safety.
- Prevents derailing during operation.
- Can rotate 90° for direct connection to hoists without intermediate hooks.
- Rubber bumpers reduce impact loads at rail ends.
- Easy Installation – 3-piece ergonomic design for quick mounting and dismounting.
- Large steel wheels with double-sided sealed bearings.
- Black powder-coated panels for long-lasting protection.
- Fits most beam profiles and lifting blocks/electric hoists.
- Temperature Range – Operates from -10°C to $+50^\circ\text{C}$.
- CE-marked, EN 13157, 4:1 safety factor.

RS PRO Push Trolley, 1000 kg Load Capacity, Adjustable for I-Beams

RS Stock No.: 0712613



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

The RS PRO Push Trolley is a high-quality, durable solution for moving loads along horizontal beams and rails. Designed for professional use, it offers easy installation, robust safety features, and compatibility with a wide range of beam profiles and hoists. Its ergonomic design, maintenance-free bearings, and shock-absorbing bumpers ensure smooth and reliable operation in industrial environments. Finished with a black powder coating, it combines strength and aesthetics for long-term performance.

General Specifications

Load Capacity (WLL)	1000 kg
Beam Compatibility	IPE, HEA, HEB, INP profiles
Finish	Black powder-coated (Matt finish)
Temperature Range	-10°C to +50°C
Installation	3-piece design, ergonomic, quick mounting
Safety Factor	4:1

Approvals

Standards Met	EN 13157, CE-marked
---------------	---------------------

Similar Products

Stock No.	Brand	Product Name	Load Capacity	Lift Height	Overload Protection
0712607	RS PRO	Lever Hoist	250 kg	1.5 m	-
0712608	RS PRO	Chain Block	2000 kg	3.0 m	Yes
0712609	RS PRO	Chain Block	500 kg	3.0 m	Yes
0712610	RS PRO	Lever Hoist	1600 kg	1.5 m	Yes
0712611	RS PRO	Lever Hoist	800 kg	1.5 m	Yes
0712612	RS PRO	Chain Block	1000 kg	3.0 m	Yes
0712613	RS PRO	Push Trolley	1000 kg	Fits I-Beams	-
0712614	RS PRO	Lever Hoist	500 kg	1.5 m	Yes
0712615	RS PRO	Lever Hoist	3200 kg	1.5 m	Yes
0712616	RS PRO	Lifting Magnet	Lifting Capacity: 600 kg	-	-