

TECHNICAL DATA

Fluke 179/TPAK Combo Kit - Includes Meter and Magnetic Hanger



Key features

The Fluke 179 has features and functions needed to troubleshoot your equipment and plant.

- True RMS AC voltage and current for accurate measurements on non-linear loads
- Large digit display with analog bargraph
- Display backlight for work in dark areas
- Temperature and capacitance
- Records minimum and maximum values to aid in troubleshooting
- Free your hands with the magnetic hanger included in this combo kit
- Durability backed up with a limited lifetime warranty
- Includes thermocouple probe, integral holster and test leads

Product overview: Fluke 179/TPAK Combo Kit - Includes Meter and Magnetic Hanger

Now you can hang your Fluke 179 True RMS Industrial Multimeter to free your hands for other use around complex machinery.

Specifications: Fluke 179/TPAK Combo Kit - Includes Meter and Magnetic Hanger

Specifications		
Voltage DC	Accuracy¹	$\pm(0.09\% + 2)$
	Max. resolution	0.1 mV
	Maximum	1000 V
Voltage AC	Accuracy¹	$\pm(1.0\% + 3)$
	Max. resolution	0.1 mV
	Maximum	1000 V
Current DC	Accuracy¹	$\pm(1.0\% + 3)$
	Max. resolution	0.01 mA
	Maximum	10 A
Current AC	Accuracy¹	$\pm(1.5\% + 3)$
	Max. resolution	0.01 mA
	Maximum	10 A
Resistance	Accuracy¹	$\pm(0.9\% + 1)$
	Max. resolution	0.1 Ω
	Maximum	50 MΩ
Capacitance	Accuracy¹	$\pm(1.2\% + 2)$
	Max. resolution	1 nF
	Maximum	10,000 µF
Frequency	Accuracy¹	$\pm(0.1\% + 1)$
	Max. resolution	0.01 Hz
	Maximum	100 kHz
Temperature	Max. resolution	0.1°C
	Range	-40°C / 400°C
1. Accuracies are best accuracies for each function		
Environmental Specifications		
Operating temperature	-10°C to +50°C	
Storage temperature	-30°C to +60°C	
Humidity (without condensation)	0% - 90% (0°C - 35°C) 0% - 70% (35°C - 50°C)	
Safety Specifications		
Overvoltage category	EN 61010-1 to 1000 V CAT III EN 61010-1 to 600 V CAT IV	

Agency approvals	UL, CSA, TÜV listed and VDE Pending
Mechanical and General Specifications	
Size	43 x 90 x 185 mm
Weight	420 g
Warranty	Lifetime
Battery life	Alkaline ~200 hours typical, without backlight

Ordering information



Fluke 179/TPAK Kit

Fluke 179/TPAK Combo Kit – Includes Meter and Magnetic Hanger

Includes:

- Fluke 179 Multimeter
- ToolPak™ Meter Hanging Kit



FLUKE®

Fluke. Keeping your world up and running.®

Fluke Corporation
PO Box 9090, Everett, WA 98206 U.S.A.

For more information call:
In the U.S.A. (800) 443-5853
In Europe/M-East/Africa +31 (0)40 267 5100
In Canada (800)-36-FLUKE
From other countries +1 (425) 446-5500

Fluke Electronics (Malaysia) Sdn Bhd
Suite D-3A-4, Block D
SouthGage Commercial Centre, No2
Jalan Dua Off Jln Chan Sow Lin
55200 KL
Malaysia
Email: info.asean@fluke.com
www.fluke.com/my
©2025 Fluke Corporation. Specifications subject to
change without notice.
12/2025

**Modification of this document is not permitted
without written permission from Fluke
Corporation.**