

SETS OF ELECTRONICS PLIERS



3-680

3-680 **BERNSTEIN** EUROline-Conductive set of pliers



4-piece set **conductive** pliers from the series EUROline-Conductive with **conductive** handguard in cases made from **conductive** black imitation leather, with zip fastener

No. **Description of individual tools** **Weight: 400 g**

- 3-651-15 **Mini side cutters EUROline-Conductive**, 120 mm, without sideface, for soft wire up to 0.6 mm Ø, copper wire up to 1.2 mm Ø, box joint, double leaf spring, fine polished and bright burnished, conductive bicoloured hand-guard
- 3-672-15 **End cutters EUROline-Conductive**, 130 mm, for copper wire up to 0.6 mm Ø, cutting edge 20° angular, box joint, double leaf spring, fine polished and bright burnished, conductive bicoloured hand-guard
- 3-682-15 **Flat nose pliers EUROline-Conductive**, 130 mm, plain jaws, finish as before
- 3-683-15 **Snipe nose pliers EUROline-Conductive**, 130 mm, plain jaws, finish as before



3-630

3-630 **BERNSTEIN** Set of conductive pliers



3-piece set bright steel-polished pliers with **conductive** handguard in a wallet of nylon

No. **Description of individual tools** **Weight: 250 g**

- 3-601-13 **Side cutters**, 120 mm, for hard wire up to 0.4 mm, for soft wire up to 1.0 mm
- 3-632-13 **Flat nose pliers**, 120 mm, plain jaws
- 3-633-13 **Snipe nose pliers**, 120 mm, plain jaws



3-960

3-960 **BERNSTEIN** Set of conductive pliers



4-piece set black burnished pliers with **conductive** handguard in a wallet of nylon

No. **Description of individual tools** **Weight: 350 g**

- 3-901-7 **Side cutters**, 120 mm, for soft wire bis 1.0 mm, for hard wire up to 0.4 mm Ø
- 3-906-7 **End cutters**, 125 mm, with angular tips and oblique cutting edge, without side face, for flush cutting, for soft wire only
- 3-932-7 **Flat nose pliers**, 120 mm
- 3-933-7 **Snipe nose pliers**, 125 mm



3-940

3-940 **BERNSTEIN** Set of pliers

4-piece set black burnished pliers with orange insulation in a wallet of nylon

No. **Description of individual tools** **Weight: 350 g**

- 3-901-12 **Side cutters**, 120 mm, for soft wire up to 1.0 mm, for hard wire up to 0.4 mm Ø
- 3-906-12 **End cutters**, 125 mm, with angular tips and oblique cutting edge, without side face, for flush cutting, for soft wire only up to 0.8 mm Ø
- 3-932-12 **Flat nose pliers**, 120 mm
- 3-933-12 **Snipe nose pliers**, 125 mm

3-930 **BERNSTEIN** Set of pliers

3-piece set black burnished pliers with orange insulation in a wallet of nylon

No. **Description of individual tools** **Weight: 275 g**

- 3-901-12 **Side cutters**, 120 mm, for soft wire up to 1.0 mm, for hard wire up to 0.4 mm Ø
- 3-932-12 **Flat nose pliers**, 120 mm
- 3-933-12 **Snipe nose pliers**, 125 mm