Specifications



Linergy FT - Comb busbar - 63 A - 2 tap-offs - 45 mm pitch

Local distributor code: 23052116

GV2G245

EAN Code: 3389110555950

Main

Range	Linergy
product name	FT
Device short name	GV2G
Product or component type	Comb busbar
Accessory / separate part category	Connection accessory
Poles description	3P
Range compatibility	TeSys GV2 TeSys Deca TeSys U
Number of tap-offs	2
[Ith] conventional free air thermal current	63 A
Connection pitch	45 mm

Complementary

Mounting location	On terminal
[Ui] rated insulation voltage	690 V
Length	89 mm
Net weight	0.036 kg

Packing Units

Number of Units in Package 11Package 1 Height2 cmPackage 1 Width4 cmPackage 1 Length9.5 cmPackage 1 Weight37 gUnit Type of Package 2S01Number of Units in Package 2100Package 2 Height15 cmPackage 2 Width15 cmPackage 2 Length40 cm	<u>U</u>	
Package 1 Height2 cmPackage 1 Width4 cmPackage 1 Length9.5 cmPackage 1 Weight37 gUnit Type of Package 2S01Number of Units in Package 2100Package 2 Height15 cmPackage 2 Width15 cmPackage 2 Length40 cm	Unit Type of Package 1	PCE
Package 1 Width4 cmPackage 1 Length9.5 cmPackage 1 Weight37 gUnit Type of Package 2S01Number of Units in Package 2100Package 2 Height15 cmPackage 2 Width15 cmPackage 2 Length40 cm	Number of Units in Package 1	1
Package 1 Length9.5 cmPackage 1 Weight37 gUnit Type of Package 2S01Number of Units in Package 2100Package 2 Height15 cmPackage 2 Width15 cmPackage 2 Length40 cm	Package 1 Height	2 cm
Package 1 Weight37 gUnit Type of Package 2S01Number of Units in Package 2100Package 2 Height15 cmPackage 2 Width15 cmPackage 2 Length40 cm	Package 1 Width	4 cm
Unit Type of Package 2 S01 Number of Units in Package 2 100 Package 2 Height 15 cm Package 2 Width 15 cm Package 2 Length 40 cm	Package 1 Length	9.5 cm
Number of Units in Package 2 100 Package 2 Height 15 cm Package 2 Width 15 cm Package 2 Length 40 cm	Package 1 Weight	37 g
Package 2 Height 15 cm Package 2 Width 15 cm Package 2 Length 40 cm	Unit Type of Package 2	S01
Package 2 Width 15 cm Package 2 Length 40 cm	Number of Units in Package 2	100
Package 2 Length 40 cm	Package 2 Height	15 cm
	Package 2 Width	15 cm
Package 2 Weight 3.862 kg	Package 2 Length	40 cm
	Package 2 Weight	3.862 kg

Unit Type of Package 3	P06
Number of Units in Package 3	3200
Package 3 Height	77 cm
Package 3 Width	80 cm
Package 3 Length	60 cm
Package 3 Weight	130.9 kg

Logistical informations

Country of origin RO

Contractual warranty

Warranty

18 months

🜔 Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

${\mathcal O}$ Environmental footprint	
--	--

Environmental Disclosure

Product Environmental Profile

Use Better

S Materials and Substances	
Packaging made with recycled cardboard	No
Packaging without single use plastic	No
EU RoHS Directive	Compliant
REACh Regulation	REACh Declaration
China RoHS Regulation	China RoHS declaration

Use Again

$^{ m \odot}$ Repack and remanufacture	
Circularity Profile	End of Life Information
Take-back	No

Product datasheet

Dimensions Drawings

Sets of Busbars $\text{GV2G}_{\bullet \bullet \bullet}$ with Terminal Block GV1G09



Sets of Busbars GV2G245, GV2G254, GV2GR272



	I
GV2G245 (2 x 45 mm)	89
GV2G254 (2 x 54 mm)	98
GV2G272 (2 x 72 mm)	116