"PanelSeT SF/SM partial 19" fixed rack - 1200 mm" Local distributor code: 385516837 NSYRCKP26

EAN Code: 3606480066917

Main

Range	PanelSeT	
Accessory / separate part category	Mounting accessory	
Product or component type	19" rack	
Application	Electronic application	
For enclosure nominal dimensions	- H: 1200 mm	
Rack type	Fixed	
Mounting location	Top front of enclosure	
Mounting support	Cross rails	
Range compatibility	PanelSeT PanelSeT SF PanelSeT PanelSeT SM	
Device composition	fixing elements 2 upright	
Quantity per set	Set of 1	
Number of units 19"	26	

Complementary

Rack coverage	Partial	
Material	Steel	
Enclosure/cubicle description	Floor-standing enclosure	
Surface finish	Zinc coated	
fixing mode	By fixing element	
Adjustment	Adjustable in depth every 25 mm	
Permanent permissible load	2 kg per unit	
Height	1200 mm	
Width	Nominal: 600 mm Nominal: 800 mm	
Depth	45 mm	

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5.000 cm
Package 1 Width	11.000 cm

Package 1 Length	116.500 cm
Package 1 Weight	3.472 kg
Unit Type of Package 2	PAL
Number of Units in Package 2	20
Package 2 Height	29.000 cm
Package 2 Width	37.500 cm
Package 2 Length	120.000 cm
Package 2 Weight	69.440 kg

Logistical informations

Country of origin FF

Contractual warranty

Coverage	Core product
Warranty	18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

☑ Environmental footprint	
Carbon footprint (kg.eq.CO2 per CR, Total Life cycle)	25
Environmental Disclosure	Product Environmental Profile

Use Better

⊗ Materials and Substances	
Packaging made with recycled cardboard	No
Packaging without single use plastic	No
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
SCIP Number	E893f0a0-d2cc-4011-9425-3873dde70142
REACh Regulation	REACh Declaration

Use Again

○ Repack and remanufacture	
Circularity Profile	No need of specific recycling operations
Take-back	No

Technical Illustration

Dimensions




Image of product / Alternate images

Alternative

