

Electrical Markets Division
3M™ Portable Labeler Refill Cartridges



Easy to Peel Labels That Stay Stuck

manufactured by:

DYMO

- Print labels meet OSHA, ANSI & ISO color standards
- Industrial-grade labels for a variety of surfaces and environments
- Choice of label materials for various surfaces that resist UV, chemicals, water & oils

3M

High-Performance Label Options for the 3M™ Portable Labeler Family

		Vinyl	Nylon	Polyester	Heat Shrink	Non-Adhesive	Self-Laminating
Labels	Length	18.0'	11.5'	18.0'	5.0'	18.0'	18.0'
	Width	3/8", 1/2", 3/4", 1"	1/2", 3/4", 1"	1/4", 3/8", 1/2", 3/4", 1"	1/4", 3/8", 1/2", 3/4"	1/4", 1/2"	1"
	Color						
	Outdoor						
Surfaces	Flat						
	Wiring						
	Flag						
	Textured						
Resistance	UV						
	Water						
	Chemicals						
	Oils						

3M™ Portable Labeler Refill Cartridges Ordering Information

3M Stock Number	Product Number	Description	UPC 0051128-	Compatibility	Color
Non-Adhesive					
80-6114-5629-6	PLNA-WHT-1/4	Non-Adhesive Tape 1/4" (6 mm). Black Font. White Label.	58493	PL150, PL200, PL300	Black
80-6114-5631-2	PLNA-WHT-1/2	Non-Adhesive Tape 1/2" (12 mm). Black Font. White Label.	58495	PL100, PL150, PL200, PL300	Black
Vinyl					
80-6114-5594-2	PLV-WHT-3/8	Vinyl Tape 3/8" (9 mm). Black Font. White Label.	58458	PL100, PL150, PL200, PL300	Black
80-6114-7037-0	PLV-WHT-BLK-3/8	Vinyl Tape 3/8" (9 mm). White Font. Black Label.	59378	PL100, PL150, PL200, PL300	White
80-6114-5595-9	PLV-WHT-1/2	Vinyl Tape 1/2" (12 mm). Black Font. White Label.	58459	PL100, PL150, PL200, PL300	Black
80-6114-5598-3	PLV-YEL-1/2	Vinyl Tape 1/2" (12 mm). Black Font. Yellow Label.	58462	PL100, PL150, PL200, PL300	Black
80-6114-5604-9	PLV-ORG-1/2	Vinyl Tape 1/2" (12 mm). Black Font. Orange Label.	58468	PL100, PL150, PL200, PL300	Black
80-6114-7038-8	PLV-WHT-BLK-1/2	Vinyl Tape 1/2" (12 mm). White Font. Black Label.	59379	PL100, PL150, PL200, PL300	White
80-6114-7051-1	PLV-WHT-RED-1/2	Vinyl Tape 1/2" (12 mm). White Font. Red Label.	59392	PL100, PL150, PL200, PL300	White
80-6114-7060-2	PLV-WHT-GRN-1/2	Vinyl Tape 1/2" (12 mm). White Font. Green Label.	59401	PL100, PL150, PL200, PL300	White
80-6114-7063-6	PLV-WHT-BLU-1/2	Vinyl Tape 1/2" (12 mm). White Font. Blue Label.	59404	PL100, PL150, PL200, PL300	White
80-6114-7066-9	PLV-WHT-PUR-1/2	Vinyl Tape 1/2" (12 mm). White Font. Purple Label.	59407	PL100, PL150, PL200, PL300	White
80-6114-7069-3	PLV-WHT-BRN-1/2	Vinyl Tape 1/2" (12 mm). White Font. Brown Label.	59410	PL100, PL150, PL200, PL300	White
80-6114-7072-7	PLV-BLK-GRY-1/2	Vinyl Tape 1/2" (12 mm). Black Font. Gray Label.	59413	PL100, PL150, PL200, PL300	Black
80-6114-5596-7	PLV-WHT-3/4	Vinyl Tape 3/4" (19 mm). Black Font. White Label.	58460	PL150, PL200, PL300	Black
80-6114-5599-1	PLV-YEL-3/4	Vinyl Tape 3/4" (19 mm). Black Font. Yellow Label.	58463	PL150, PL200, PL300	Black
80-6114-5605-6	PLV-ORG-3/4	Vinyl Tape 3/4" (19 mm). Black Font. Orange Label.	58469	PL150, PL200, PL300	Black
80-6114-7039-6	PLV-WHT-BLK-3/4	Vinyl Tape 3/4" (19 mm). White Font. Black Label.	59380	PL150, PL200, PL300	White
80-6114-7052-9	PLV-WHT-RED-3/4	Vinyl Tape 3/4" (19 mm). White Font. Red Label.	59393	PL150, PL200, PL300	White
80-6114-7061-0	PLV-WHT-GRN-3/4	Vinyl Tape 3/4" (19 mm). White Font. Green Label.	59402	PL150, PL200, PL300	White
80-6114-7064-4	PLV-WHT-BLU-3/4	Vinyl Tape 3/4" (19 mm). White Font. Blue Label.	59405	PL150, PL200, PL300	White
80-6114-7067-7	PLV-WHT-PUR-3/4	Vinyl Tape 3/4" (19 mm). White Font. Purple Label.	59408	PL150, PL200, PL300	White
80-6114-7070-1	PLV-WHT-BRN-3/4	Vinyl Tape 3/4" (19 mm). White Font. Brown Label.	59411	PL150, PL200, PL300	White
80-6114-7073-5	PLV-BLK-GRY-3/4	Vinyl Tape 3/4" (19 mm). Black Font. Gray Label.	59414	PL150, PL200, PL300	Black
80-6114-7036-2	PLV-BLK-WHT-1	Vinyl Tape 1" (24 mm). Black Font. White Label.	59381	PL300	Black
80-6114-7059-4	PLV-BLK-YEL-1	Vinyl Tape 1" (24 mm). Black Font. Yellow Label.	59400	PL300	Black
80-6114-7056-0	PLV-BLK-ORG-1	Vinyl Tape 1" (24 mm). Black Font. Orange Label.	59397	PL300	Black
80-6114-7040-4	PLV-WHT-BLK-1	Vinyl Tape 1" (24 mm). White Font. Black Label.	59381	PL300	White
80-6114-7053-7	PLV-WHT-RED-1	Vinyl Tape 1" (24 mm). White Font. Red Label.	59392	PL300	White
80-6114-7062-8	PLV-WHT-GRN-1	Vinyl Tape 1" (24 mm). White Font. Green Label.	59403	PL300	White
80-6114-7065-1	PLV-WHT-BLU-1	Vinyl Tape 1" (24 mm). White Font. Blue Label.	59404	PL300	White
80-6114-7068-5	PLV-WHT-PUR-1	Vinyl Tape 1" (24 mm). White Font. Purple Label.	59407	PL300	White
80-6114-7071-9	PLV-WHT-BRN-1	Vinyl Tape 1" (24 mm). White Font. Brown Label.	59410	PL300	White
80-6114-7074-3	PLV-BLK-GRY-1	Vinyl Tape 1" (24 mm). Black Font. Gray Label.	59413	PL300	Black

Ordering information continued on back.



3M™ Portable Labeler Refill Cartridges Ordering Information

3M Stock Number	Product Number	Description	UPC 0051128-	Compatibility	Color
Polyester					
80-6114-7042-0	PLP-BLK-WHT-1/4	Polyester Tape 1/4' (6 mm). Black Font. White Label.	59383	PL150, PL200, PL300	Black
80-6114-7046-1	PLP-BLK-MTL-1/4	Polyester Tape 1/4' (6 mm). Black Font. Metal Label.	59387	PL150, PL200, PL300	Black
80-6114-7041-2	PLP-BLK-CLR-1/4	Polyester Tape 1/4' (6 mm). Black Font. Clear Label.	59382	PL150, PL200, PL300	Black
80-6114-5621-3	PLP-WHT-3/8	Polyester Tape 3/8" (9 mm). Black Font. White Label.	58485	PL150, PL200, PL300	Black
80-6114-5628-8	PLP-MTL-3/8	Polyester Tape 3/8" (9 mm). Black Font. Metal Label.	58492	PL150, PL200, PL300	Black
80-6114-5625-4	PLP-CLR-3/8	Polyester Tape 3/8" (9 mm). Black Font. Clear Label.	58489	PL150, PL200, PL300	Black
80-6114-5622-1	PLP-WHT-1/2	Polyester Tape 1/2" (12 mm). Black Font. White Label.	58486	PL150, PL200, PL300	Black
80-6114-5626-2	PLP-MTL-1/2	Polyester Tape 1/2" (12 mm) Black Font. Metal Label.	58490	PL150, PL200, PL300	Black
80-6114-5642-9	PLP-CLR-1/2	Polyester Tape 1/2" (12 mm). Black Font. Clear Label.	58506	PL150, PL200, PL300	Black
80-6114-5623-9	PLP-WHT-3/4	Polyester Tape 3/4" (19 mm). Black Font. White Label.	58487	PL150, PL200, PL300	Black
80-6114-5627-0	PLP-MTL-3/4	Polyester Tape 3/4" (19 mm). Black Font. Metal Label.	58491	PL150, PL200, PL300	Black
80-6114-5643-7	PLP-CLR-3/4	Polyester Tape 3/4" (19 mm). Black Font. Clear Label.	58507	PL150, PL200, PL300	Black
80-6114-5624-7	PLP-WHT-1	Polyester Tape 1" (24 mm). Black Font. White Label.	58488	PL300	Black
80-6114-7050-3	PLP-BLK-MTL-1	Polyester Tape 1" (24 mm). Black Font. Metal Label.	59391	PL300	Black
80-6114-7045-3	PLP-BLK-CLR-1	Polyester Tape 1" (24 mm). Black Font. Clear Label.	59386	PL300	Black
Flexible Nylon					
80-6114-5645-2	PLFN-WHT-1/2	Flexible Nylon Tape 1/2" (12 mm). Black Font. White Label.	58509	PL150, PL200, PL300	Black
80-6114-5648-6	PLFN-YEL-1/2	Flexible Nylon Tape 1/2" (12 mm). Black Font. Yellow Label.	58512	PL150, PL200, PL300	Black
80-6114-5646-0	PLFN-WHT-3/4	Flexible Nylon Tape 3/4" (19 mm). Black Font. White Label.	58510	PL150, PL200, PL300	Black
80-6114-5649-4	PLFN-YEL-3/4	Flexible Nylon Tape 3/4" (19 mm). Black Font. Yellow Label.	58513	PL150, PL200, PL300	Black
80-6114-5647-8	PLFN-WHT-1	Flexible Nylon Tape 1" (24 mm). Black Font. White Label.	58511	PL300	Black
80-6114-5650-2	PLFN-YEL-1	Flexible Nylon Tape 1" (24 mm). Black Font. Yellow Label.	58514	PL300	Black
Self-Laminating					
80-6114-5728-6	PLSL-WHT-1	Self-Laminating Tape 1" (24 mm). Black Font. White Label.	58583	PL300	Black
Heat Shrink					
80-6114-5619-7	PLHS-WHT-1/4	Heat Shrinking Tubing 1/4" (6 mm). Black Font. White Label.	58483	PL200, PL300	Black
80-6114-5611-4	PLHS-WHT-3/8	Heat Shrinking Tubing 3/8" (9 mm). Black Font. White Label.	58475	PL150, PL200, PL300	Black
80-6114-5612-2	PLHS-WHT-1/2	Heat Shrinking Tubing 1/2" (12 mm). Black Font. White Label.	58476	PL150, PL200, PL300	Black
80-6114-5613-0	PLHS-WHT-3/4	Heat Shrinking Tubing 3/4" (19 mm). Black Font. White Label.	58477	PL200, PL300	Black
80-6114-5620-5	PLHS-YEL-1/4	Heat Shrinking Tubing 1/4" (6 mm). Black Font. Yellow Label.	58484	PL200, PL300	Black
80-6114-5614-8	PLHS-YEL-3/8	Heat Shrinking Tubing 3/8" (9 mm). Black Font. Yellow Label.	58478	PL150, PL200, PL300	Black
80-6114-5615-5	PLHS-YEL-1/2	Heat Shrinking Tubing 1/2" (12 mm). Black Font. Yellow Label.	58479	PL150, PL200, PL300	Black
80-6114-5616-3	PLHS-YEL-3/4	Heat Shrinking Tubing 3/4" (19mm). Black Font. Yellow Label.	58480	PL200, PL300	Black

3M is a trademark of 3M Company. DYMO is a trademark of Newell Rubbermaid.

Important Notice

Before utilizing any of 3M's products, you should determine the suitability of the product for your intended use. You assume all risks and liability associated with such use.

Warranty; Limited Remedy; Limited Liability.

This product will be free from defects in material and manufacture for a period of thirty (30) days from the time of purchase. If this product is defective, your exclusive remedy shall be, at 3M's option, to replace the 3M product or refund the purchase price. Except where prohibited by law, 3M will not be liable for any indirect, special, incidental or consequential loss or damage arising from this 3M product, regardless of the legal theory asserted.



Electrical Markets Division

6801 River Place Blvd.
Austin, TX 78726-9000
800 245 3573
FAX 800 245 0329
www.3M.com/electrical

© 3M 2011. All rights reserved.
80-6016-0426-9 (081010.0) GP