



PRODUCT-DETAILS

MSHD-LTY

MSHD-LTY Handle, IP64, red/yellow, 3 times lockable, defeatable, 0-TRIP-I



概要信息	
产品型号	MSHD-LTY
产品ID	1SAM201920R1012
欧洲商品编号(EAN)	4013614441844
目录说明	MSHD-LTY Handle, IP64, red/yellow, 3 times lockable, defeatable, 0-TRIP-I
详细描述	Handles MSHD can be used in door coupling solutions for operating manual motor starters MS116, MS132 or MS165 in the back of a switch cabinet from outside. They are by design padlockable only in OFF-position (with max. 3 padlocks). MSHD can be used with shafts OXS6 from 6 mm up to 180 mm or driver shafts MSOX. Their degree of protection is IP64. Handles MSHD are available in yellow and black color and with or without Trip position.

订货信息	
最小起订量	1 piece
海关关税号	85389099

Popular Downloads

数据手册，技术资料	1SBC100173C0201
说明书和手册	2CDC131033M6801
CAD Dimensional Drawing	2CDC001079B0201

尺寸

产品净宽	65.6 mm
产品净高	65.5 mm
产品净深	57.9 mm
产品净重	0.065 kg

技术参数

触头位置指示	ON / OFF / TRIP
驱动器类型	Rotary Handle
轴径	6x6 mm
颜色	yellow / red
防护等级	IP64
拧紧力矩	0.12 N·m
产品	Handles
适用于	MS132 MO132 MS450 MS451 MS495 MS496 MS497 MO450 MO495 MO496
适用产品系列	Manual Motor Starter
配件组别	Mechanical
配件类型	Handles

UL/CSA适用的技术参数

外壳类型UL/CSA	1 12 3R
拧紧力矩UL/CSA	1.06 in·lb

Material Compliance

Conflict Minerals Reporting Template (CMRT)	9AKK108467A5658
REACH Declaration	1SAA963005-4502
RoHS信息	1SAA963006-4502
RoHS状态	Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019
Toxic Substances Control Act - TSCA	2CMT2023-006539
WEEE 类别	Product Not in WEEE Scope

认证及声明（文件编码）	
符合性声明 - CE	1SAD101100-3411
Declaration of Conformity - UKCA	1SAD201100-3411

包装信息	
1级包装宽度	130 mm
1级包装长度	70 mm
1级包装高度	170 mm
1级包装 总重	0.1 kg
1级包装 EAN	4013614441844
1级包装单元	box 1 piece

分类	
对象分类代码	X
ETIM 4	EC002498 - Accessories for low-voltage switch technology
ETIM 5	EC000229 - Handle for power circuit breaker
ETIM 6	EC000229 - Handle for power circuit breaker
ETIM 7	EC000229 - Handle for power circuit breaker
ETIM 8	EC000229 - Handle for power circuit breaker
e级	V11.0 : 27370414
UNSPSC	31162801
IDEA 粒度分类代码 (IGCC)	3038 >> Handles or knobs
E-Number (Finland)	3705867
E-Number (Norway)	4364253

Accessories				
Identifier	Description	Type	Quantity	Unit Of Measure
1SAM201920R1000	MSH-AR Shaft alignment ring suitable for MSHD and MSH handles	MSH-AR	1	piece
1SAM101923R0002	MSMN Driver w. screw for manual motor staters, 6x6	MSMN	1	piece
1SAM101923R0012	MSMNO Driver w/o coding w. screw for manual motor staters, 6x6	MSMNO	1	piece
1SCA101647R1001	OXS6X85 SHAFT	OXS6X85	1	piece
1SCA108043R1001	OXS6X105 SHAFT	OXS6X105	1	piece
1SCA101655R1001	OXS6X130 SHAFT	OXS6X130	1	piece
1SCA101659R1001	OXS6X180 SHAFT	OXS6X180	1	piece

分类

低压产品及系统 → 控制产品 → 电动机起动器 → 电动机起动器

低压产品及系统 → 断路器类产品 → 电动机起动器

