

1504 XL-TS-308

Workbench with tool assortment

308 pieces

Code	ETIM
2980355	EC000149
EAN	UNSPSC
4010886948484	56-12-18-02
Country of origin	eCl@ss
Germany	21-10-02-00
Customs tariff number	
82060000	



Article description

- For industry, the trades, automotive
- Tools in metric dimensions
- GEDORE Check-Tool-System: 2-colour foam insert to check that the set is complete
- Resistant against oils and grease
- In workbench No. 1504 XL
- 30 mm thick multiplex beech plywood board, surface additionally protected by linseed oil varnish
- Large storage space with shelf and door
- Safety through heel protection for persons
- Central locking with cylinder lock
- 1 XL drawer (W 1055 x D 400 mm), 6 wide drawers (W 640 x D 400 mm) with full extension, removable
- Safety lock per drawer, one-hand operation
- Ball-bearing guide rails
- Load capacity per drawer 40 kg, bottom heavy-duty drawer 60 kg
- Total load capacity 1000 kg, 750 kg when mobile
- 2 GEDORE high-performance wheels with roller bearings (fixed castors Ø 200 mm)
- 2 ball-bearing GEDORE smooth-running wheels (swivel castors Ø 125 mm), both with total brake
- GEDORE trapezoidal axle construction ensures smooth running, manoeuvrability and directional stability even under maximum load
- Expandable with rear panel No. R 1504 XL-L
- Dimensions: H 985 x B 1250 x T 630 mm

Article parts list

1/4"+1/2" socket wrench assortment in CT module No. TS CT2-D19-D20, 81 pcs, Combination wrench set in CT module No. TS CT2-7, 24 pcs, Tool assortment in CT module No. TS CT2-21545K-119, 14 pcs., Pliers assortment in CT module No. TS CT2-142, 28 pcs., Tool assortment in 2/4 CT module No. TS CT2-6-8000, 15 pcs., 1/2" set of screwdriver sockets in 2/4 CT module No. TS CT2-ITX19, 28 pcs., Tool assortment in 2/4 CT module No. TS CT2-2133-2163TX, 13 pcs, Wrench set in 2/4 CT module No. TS CT2-7R-2, 28 pcs, Tool assortment in 2/4 CT module No. TS CT2-D30, 59 pcs, Tool assortment in 2/4 CT module No. TS CT2-710, 17 pcs, Hacksaw No. 407, + mobile workbench No. 1504 XL, 1,25 m wide

Article information

Contents (Qty of pieces)	308	Material	Sheet steel
Net weight [kg]	148,6 kg	Number of drawers	7
Total width [mm]	1.250 mm	Drawer type	1x Type 1, H. = 67 mm extra large 4x Type 2, H. = 67 mm 1x Type 3, H. = 137 mm 1x Type 4, H. = 207 mm
Total height [mm]	985 mm	Single pull-out stop	no
Total depth [mm]	630 mm		