








OSRAM LED ValueFlex LED Strip Selector

Driver type by length required

Drivers

Type	Strip Options	Driver Type	Driver type by length required						Drivers		
			1M	2M	3M	4M	5M	6M	30	80	
300 Lumens, 2.0W/M IP20, IP66 6M	VF300-G3-827-06 171-6182 VF300-G3-840-06 171-6183 VF300-G3-865-06 171-6184 VFP300-G3-827-06 171-6185 VFP300-G3-840-06 171-6186 VFP300-G3-865-06 171-6187	On-Off Driver							ELEMENT 30/220-240/24 134-8597	ELEMENT 60/220-240/24 134-8598	OT 80/220-240/24 DIM P 760-6188
		1-10V Driver									
1200 Lumens, 10.0W/M IP20, IP66 6M	VF1200S-G3-827-06 171-6189 VF1200S-G3-840-06 171-6190 VF1200S-G3-865-06 171-6191 VFP1200S-G3-827-06 171-6192 VFP1200S-G3-840-06 171-6193 VFP1200S-G3-865-06 171-6195	On-Off Driver							ELEMENT 30/220-240/24 134-8597	ELEMENT 60/220-240/24 134-8598	OT 80/220-240/24 DIM P 760-6188
		1-10V Driver									
2400 Lumens, 20.0W/M IP20, IP66 3M	VF2400S-G3-827-06 171-6196 VF2400S-G3-840-06 171-6197 VF2400S-G3-865-06 171-6198 VFP2400S-G3-827-06 171-6199 VFP2400S-G3-840-06 171-6200 VFP2400S-G3-865-06 171-6201	On-Off Driver			n/a				ELEMENT 30/220-240/24 134-8597	ELEMENT 60/220-240/24 134-8598	OT 80/220-240/24 DIM P 760-6188
		1-10V Driver									
Power Feeders and Strip to Strip Connectors		Feeder IP20 Strip To Driver Connector 171-6202									
		Feeder IP54 Strip To Driver Connector 171-6203									
		Jumper IP54 & IP20 In-Line Strip to Strip Connector 171-6204									
Profiles & Accessories		Profile: LF-LTS-2100 134-8592									
		Profile Diffuser Frosted: LF-LTS COVER 134-8595									
		Profile End Cap: LF-LTS-ENDCAP 134-8594									
		Profile Mounting Bracket: LF-LTS-MB 134-8593									
Colour Definitions to aide selection		827 = Very Warm White						Yellower: For warm home lighting in kitchens, living rooms, Bedrooms etc - Matches colour of filament lamps			
		840 = Cool White						Whiter: For whiter light such as bathrooms, hair salons and offices - Matches typical office fluorescent colour			
		865 = Daylight						Bluer White: For very white light such as Laboratories, Dentists and sterile environments			