


FEATURES

- Chrome vanadium construction with chrome molybdenum steel sockets
- Supplied in a handy blow moulded carry case

RS PRO 94 Piece Mechanical Tool Kit with Case

RS Stock No.: 734-8889



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

RS PRO mechanics 94 piece tool kit, offering various hand tools to make a comprehensive kit. The tools are of dependable quality. Designed for professional mechanics and serious DIY experts. The easy to carry case is versatile and durable with cut-out slots created for each individual component. The kit itself contains a useful selection of sockets, spanners, universal joints, hex bit couplers, hex bits, precision screwdrivers and extension bars in various sizes.

General Specifications

Set Type	Mechanical
Set Contents	Bits, Precision Screwdriver, Ratchet, Screwdriver, Sockets, Spanners
Number of Pieces	94
Storage Type	Case
Applications	Mechanic, Home use

Mechanical Specifications

Tool Case Dimension	400mm x 315mm x 86mm
----------------------------	----------------------

Kit Contains

Name
1/2" Sockets 13mm, 14mm, 15mm, 16mm, 17mm, 18mm, 19mm, 20mm, 21mm, 22mm, 23mm, 24mm, 27mm, 30mm, 32mm
1/4" Sockets Spark Plug Sockets 4mm, 4.5mm, 5mm, 5.5mm, 6mm, 7mm, 8mm, 9mm, 10mm, 11mm, 12mm, 13mm
1/2" Quick Release Ratchet
1/4" Quick Release Ratchet
1/2" Universal Joint (Rivet Type)
1/4" Universal Joint (Rivet Type)
3/8" T-bar Adapter
1/4" 110mm Sliding T-bar
1/2" Quick Release Ratchet Extension Bars
Combination Spanners 8mm, 10mm, 11mm, 12mm, 13mm, 14mm, 17mm, 19mm, 22mm
Precision Screwdrivers Slotted: 1.5mm, 2mm, 3mm
Precision Screwdrivers Phillips: No.0-0mm, No.0mm, No. 1
Precision Screwdrivers Torx: T6, T8, T10
Screwdriver Bits 25 (L) x 6.35mm Hexagon Bits Slotted: 4mm, 5mm, 6mm
Screwdriver Bits 25 (L) x 6.35mm Hexagon Bits Phillips: No.1mm, No.2
Screwdriver Bits 25 (L) x 6.35mm Hexagon Bits Pozi: No.1mm, No.2
Screwdriver Bits 25 (L) x 6.35mm Hexagon Bits Hex Bits: 3mm, 4mm, 5mm
Screwdriver Bits 25 (L) x 6.35mm Hexagon Bits Torx: T10mm, T15mm, T20mm, T25mm, T27mm, T30
Screwdriver Bits 30 (L) x 10mm Hexagon Bits Slotted: 7mm, 8mm, 10mm
Screwdriver Bits 30 (L) x 10mm Hexagon Bits Phillips: No.3mm, No.4
Screwdriver Bits 30 (L) x 10mm Hexagon Bits Pozi: No.3mm, No.4
Screwdriver Bits 30 (L) x 10mm Hexagon Bits Hex Bits: 6mm, 7mm, 8mm, 10mm
Screwdriver Bits 30 (L) x 10mm Hexagon Bits Torx: T30mm, T40mm, T45mm, T47mm, T50
Spark Plug Sockets 16mm and 21mm
Extension Bars 1/2" 125mm and 250mm
Extension Bars 1/4" 55mm, 100mm and 250mm
1/4" 150mm Spinner
1/4" Screwdriver Bit Coupler
1/2" Screwdriver Bit Coupler
Blow Moulded Case

Approvals

VDE/1000V Approved	No
--------------------	----

