


543980 DGSL-12-80-Y3A Mini slide - Series from 08-2022



543980 DGSL-12-80-Y3A Mini slide - Series from 08-2022

Pos.	Part no.	Type	Note	Qty.	Unit
A	713747	DGSL-12-...- Set of wearing parts	Spare parts: 5, 6, 8, 11, 27, 30, 35, 36, 37, 38, 41, 46, 47	1	PC
1	200664	ISO 4762-M4X16-8.8 Socket head screw	Tightening torque 2.9 Nm / 2.1 lbf ft Use locking compound. See position 47	1	PC
2	696369	DGSL-12 Shaft screw	Tightening torque 3.6 Nm / 2.7 lbf ft	2	PC
3		DGSL-12 Yoke plate	Not available separately, see position 9 Glue with Loctite 401, adhesion surface area must free of oil and grease Warning! Disassembly requires recalibration.	1	PC
4		DGST-12/16 Centring sleeve	Not available separately, see position 9 Glue with Loctite 401, adhesion surface area must free of oil and grease Warning! Disassembly requires recalibration.	1	PC
5		SB-18 Circlip	Not available separately, see position 9+999	1	PC
6		WIFC1-6X9X2,8-TPE-U Wiper seal	Not available separately, see position 9+999 Grease using during assembly. See position 46	1	PC
7		DGSL-12 Bearing cap	Not available separately, see position 9 Grease using during assembly. See position 46	1	PC
8		B-14X1-N-NBR75 O-ring ISO3601	Not available separately, see position 9+999 Grease using during assembly. See position 46	1	PC
9	8197196	DGSL-12 Set of components		1	PC
10		DGSL-12-80 Guide module	Not available Use locking compound. See position 47	1	PC
11	200675	ISO 4762-M5X30-8.8 Socket head screw		1	PC
12	686786	DGSL-12 Stop		1	PC
13	686802	DGSL-12 Covering		1	PC
14	209537	ISO 4762-M4X8-8.8 Socket head screw	Tightening torque 2.9 Nm / 2.1 lbf ft	1	PC
15	8145638	DGSL-12 Moment compensator		1	PC
16		ISO 4762-M4X16-10.9 Socket head screw	Not available Tightening torque 3.6 Nm / 2.7 lbf ft	2	PC
17	699255	DGSL-12 Clamping component	Use locking compound. See position 47	2	PC
18	371075	7,5X9,0 Buffer element		1	PC
19		DYEF-S-M10-Y1 adjustment sleeve	Not available separately, see position 20	1	PC
20	1152959	DYEF-S-M10-Y1 Shock absorber	shock absorber -E	2	PC
21	371075	7,5X9,0 Buffer element		1	PC
22		DGSL-12-P adjustment sleeve	Not available separately, see position 23	1	PC
23	1179837	DYEF-M10-Y1 Shock absorber	shock absorber -P	2	PC
24	683974	DGSL-12/16/20-PFJ Buffer		1	PC
25		DGSL-12-P1 adjustment sleeve	Not available separately, see position 26	1	PC

Pos.	Part no.	Type	Note	Qty.	Unit
26	548374	DYEF-M10-Y1F Shock absorber	shock absorber -P1	2	PC
27	710133	DYSC-7-5-Y1F Buffer		1	PC
28		DYSW-7-10-Y1F Shock absorber	Not available separately, see position 29	1	PC
29	548072	DYSW-7-10-Y1F Shock absorber	shock absorber -Y3	2	PC
30	707464	DYSC/W-5- Buffer		1	PC
31		DYSW-5-8-Y1F Shock absorber	Not available separately, see position 32	1	PC
32	548071	DYSW-5-8-Y1F Shock absorber	Attention, please order position 33 as well shock absorber -Y3	2	PC
33	1165480	DAYH-5 reducing sleeve	Attention, please order position 32 as well shock absorber -Y11	2	PC
34	689220	IRA-06-S0133,4-B Piston rod	Glue with Loctite 401, adhesion surface area must free of oil and grease Warning! Disassembly requires recalibration.	1	PC
35		BA-K10D-016-A Complete piston	Not available separately, see position A Grease using during assembly. See position 46	1	PC
36	709440	DSNU-16 Nut	Tightening torque 1.5 Nm / 1.1 lbf ft Use locking compound. See position 47	1	PC
37		B-14X1-N-NBR75 O-ring ISO3601	Not available separately, see position A Grease using during assembly. See position 46	1	PC
38		B-5X1,5-N-NBR75 O-ring ISO3601	Not available separately, see position A Grease using during assembly. See position 46	1	PC
39		DGSL-12 Flow control plate	Not available separately, see position 44	2	PC
40		DGSL-12 Connection cap	Not available separately, see position 44	1	PC
41		OK-M5 Sealing ring	Not available separately, see position 43+999	1	PC
42		B-M5 B Plug screw	Not available separately, see position 43 Tightening torque 2 Nm / 1.5 lbf ft	1	PC
43	712005	B-M5-B-OK Blanking plug		2	PC
44	714231	DGSL-12-...-ET Connection cover module		1	PC
45	200666	ISO 4762-M4X30-8.8 Socket head screw	Tightening torque 2.3 Nm / 1.7 lbf ft Use locking compound. See position 47	3	PC
46	684474	LUB-KC1 SILIKONFREI 20ML Lubricating grease		1	PC
47	8181256	CYBERBOND TM44 TB1ML Adhesive bonding agent		1	PC