



Coil & Din Plug to suite Pneumatic Valves:

Coil & Din Plug to suite Process Solenoid Valves:

Options: IECEX, ATEX, Flying Leads - Contact RS

Options: IECEX, ATEX, Flying Leads - Contact RS

RS Part #	Coil Series by Voltage	MPN
4V1 Series 3V1 Series	 CDA080 CDA080	
635-474 635-475 635-477 635-478 635-479	 AC 220 V - CDA080A DC 24 V - CDA080B AC 110 V - CDA080C AC 24V - CDA080E DC 12V - CDA080F	CDA080A CDA080B CDA080C CDA080E CDA080F
4M31/4M32 3V2 / 3V3 Series 4V2 Series	 CDA092 CDA092 CDA092	
635-480 635-481 635-483 635-423 635-424	 AC 220 V - CDA092A DC 24 V - CDA092B AC 110 V - CD092C AC 24V - CD092E DC 12 V - CD092F	CDA092A CDA092B CDA092C CDA092E CDA092F
635-463 635-516 635-464	 80 Series Din Plugs - 15mm Square Mini Plug Black Din PLUG To Suite AC/DC - PL1515T-P1 LED Din PLUG for AC Coil - PL1515T-P2 LED Din PLUG for DC Coil - PL1515T-P3	PL1515T-P1 PL1515T-P2 PL1515T-P3
811-8263	92 Series Din Plug - 22mm Rectangular Plug Black Din Plug to suite 92 series coil **LED Din Plugs available - contact RS CS**	

RS Part #	Coil Series by Voltage	MPN
2WA in sizes (1/8" & 1/4") 2WA in sizes (3/8" & 1/2")	CDA110 CDA160	
2SA030 Series 2SA050 Series 2SA150 Series 2SA200 Series 2SA250 Series 2SA300 Series	CDA110 CDA160 CDA110 CDA110 CDA110 CDA160	
635-425 635-427 635-428 635-429 635-430 635-431 635-433 635-434 635-435 635-436	Coil NC CDA110A 220VAC Coil NC CDA110B 24DC Coil NC CDA110C 110VAC Coil NC CDA110E 12VDC Coil NC CDA110F 24VAC Coil NC CDA160A 220VAC Coil NC CDA160B 24DC Coil NC CDA160C 110VAC Coil NC CDA160E 12VDC Coil NC CDA160F 24VAC	CDA110A CDA110B CDA110C CDA110E CDA110F CDA160A CDA160A CDA160C CDA160E CDA160F
		
	635-517 2WA030-005-P1 Black Din PLUG	2WA030-005-P1