

CRIMPFOX 25R CUS - Crimping pliers



1212765

<https://www.phoenixcontact.com/in/products/1212765>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Crimping pliers, laser marked according to customer specifications, for ferrules according to DIN 46228 Parts 1+4, 10 mm² ... 25 mm², lateral entry, WM crimp

Your advantages

- Ergonomically designed handles ensure an optimum grip and reduce the amount of force required by 25 %

Commercial data

Item number	1212765
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	BH3
Product key	BH313V
Catalog page	Page 473 (C-3-2019)
GTIN	4046356942928
Weight per piece (including packing)	681.4 g
Weight per piece (excluding packing)	680.1 g
Customs tariff number	82032000
Country of origin	SE

CRIMPFOX 25R CUS - Crimping pliers



1212765

<https://www.phoenixcontact.com/in/products/1212765>

Technical data

Notes

Environmental Product Compliance

California Proposition 65	Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration
---------------------------	---

Product properties

Product type	Crimping tool
Compression	WM crimp

Connection data

Conductor connection

Cross section range, metric	10 mm ² ... 25 mm ²
Cross section range AWG	8 ... 4

Dimensions

Width	25 mm
Height	68 mm
Length	256 mm

CRIMPFOX 25R CUS - Crimping pliers



1212765

<https://www.phoenixcontact.com/in/products/1212765>

Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/in/products/1212765>



EAC

Approval ID: RU x-DE.xx08.B.02974

CRIMPFOX 25R CUS - Crimping pliers



1212765

<https://www.phoenixcontact.com/in/products/1212765>

Classifications

ECLASS

ECLASS-11.0	21043811
ECLASS-12.0	21043811
ECLASS-13.0	21043811

ETIM

ETIM 9.0	EC000168
----------	----------

UNSPSC

UNSPSC 21.0	27111500
-------------	----------

CRIMPFOX 25R CUS - Crimping pliers



1212765

<https://www.phoenixcontact.com/in/products/1212765>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

CRIMPFOX 25R CUS - Crimping pliers

1212765

<https://www.phoenixcontact.com/in/products/1212765>



Accessories

CRIMPFOX/ SPR-1 - Replacement spring

1212069

<https://www.phoenixcontact.com/in/products/1212069>



Spare recuperating spring

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT (I) Pvt. Ltd.
A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420
info@phoenixcontact.co.in