

- Fits TORX® and Star screws
- Fits in both TORX® and TORX PLUS® fasteners
- A full range of tip sizes from T5 to T100
- The only TORX® tools made with Protanium® steel



L-Wrenches



Wing and Flag Tools



Fold Ups



T-Handles

Color-Coded  
 TORX®



Screwdrivers



Socket Bits

Bondhus TORX® tools are made to the same high standards as every tool we make. Our TORX® tools are precision machined, available in many handle and tip types, and are the only TORX® tools made from Protanium® High Torque Steel. Bondhus TORX® tools fit both TORX® and Star screws.

**BONDHUS**  
**LIFETIME WARRANTY**  
 If any Bondhus® tool breaks or fails to meet your expectations in any way, simply return it. We will replace it free of charge.



High Torque Steel:


Up to 20% stronger, with more torque and twice the wear resistance of standard grades of steel.

**FINISH OPTIONS:**



Corrosion-resistant finish:

Environmentally safe, provides better tool grip, resists solvents and is 5 times more corrosion resistant than competitor finishes.

**L-Wrenches**


PART#	MODEL#	PCS	LENGTH	CONTENTS	QTY
31832	TLX8S	8	Long	T6, T7, T8, T9, T10, T15, T20, T25	1
31834	TLX8	8	Long	T9, T10, T15, T20, T25, T27, T30, T40	1
31732	TLXS8S	8	Short	T6, T7, T8, T9, T10, T15, T20, T25	1
31734	TLXS8	8	Short	T9, T10, T15, T20, T25, T27, T30, T40	1
12699	TLX9S	9	Short	T10, T15, T20, T25, T27, T30, T40, T45, T50 (in pouch)	1
31737	TLX13S	13	Short	T7, T8, T9, T10, T15, T20, T25, T27, T30, T40, T45, T50, T55 (in pouch)	1

**ProHold® L-Wrenches**


PART#	MODEL#	PCS	LENGTH	CONTENTS	QTY
71834	PHTX8	8	Long	T9, T10, T15, T20, T25, T27, T30, T40	1

**BallStar™ Tip L-Wrenches**


PART#	MODEL#	PCS	LENGTH	CONTENTS	QTY
11346	LTX6	6	Long	T6, T7, T8, T9, T10, T15	1
11331	LTX8S	8	Long	T6, T7, T8, T9, T10, T15, T20, T25	1
11332	LTX8	8	Long	T9, T10, T15, T20, T25, T27, T30, T40	1

**Tamper Resistant L-Wrenches**


PART#	MODEL#	PCS	LENGTH	CONTENTS	QTY
32432	TR-TL8S	8	Long	TR6, TR7, TR8, TR9, TR10, TR15, TR20, TR25	1
32434	TR-TL8	8	Long	TR9, TR10, TR15, TR20, TR25, TR27, TR30, TR40	1

**GorillaGrip® Fold Ups**


PART#	MODEL#	PCS	CONTENTS	QTY
12632	TF8S	8	T6, T7, T8, T9, T10, T15, T20, T25	1
12634	TF8	8	T9, T10, T15, T20, T25, T27, T30, T40	1

**Tamper Resistant GorillaGrip® Fold Ups**


PART#	MODEL#	PCS	CONTENTS	QTY
12636	TR-TF7S	7	TR7, TR8, TR9, TR10, TR15, TR20, TR25	1
12638	TR-TF8	8	TR9, TR10, TR15, TR20, TR25, TR27, TR30, TR40	1

**T-Handles**


PART#	MODEL#	PCS	LENGTH	W/STAND	CONTENTS	QTY
33034 ✓	TTHX8	8	Graduated	✓	T9, T10, T15, T20, T25, T27, T30, T40	1

**ProHold® T-Handles**


PART#	MODEL#	PCS	LENGTH	W/STAND	CONTENTS	QTY
74034 ✓	PHTTHX8	8	Graduated	✓	T9, T10, T15, T20, T25, T27, T30, T40	1

**Screwdrivers**


PART#	MODEL#	PCS	CONTENTS	QTY
34532	TSX8S	8	T6, T7, T8, T9, T10, T15, T20, T25	1
34534	TSX8	8	T9, T10, T15, T20, T25, T27, T30, T40	1

**ProHold® Screwdrivers**


PART#	MODEL#	PCS	CONTENTS	QTY
75534	PHTSX8	8	T9, T10, T15, T20, T25, T27, T30, T40	1

**BallStar™ Tip Screwdrivers**


PART#	MODEL#	PCS	CONTENTS	QTY
13546	STX6	6	T6, T7, T8, T9, T10, T15	1
13532	STX8	8	T9, T10, T15, T20, T25, T27, T30, T40	1

**Tamper Resistant Screwdrivers**


PART#	MODEL#	PCS	CONTENTS	QTY
33832	TR-SX8S	8	TR6, TR7, TR8, TR9, TR10, TR15, TR20, TR25	1
33834	TR-SX8	8	TR9, TR10, TR15, TR20, TR25, TR27, TR30, TR40	1

✓ Comes with stand

**Bondhus Corporation**

1400 E Broadway • PO Box 660 • Monticello, MN 55362  
 Tel: 763-295-2162 • Toll Free: 800-328-8310 • Fax: 763-295-4440

TORX® and TORX PLUS® are registered trademarks of Acument Intellectual Properties, LLC.

Bondhus, Protanium, ProGuard, BallStar and GorillaGrip are trademarks of Bondhus Corporation.

Distributed by: