



Foot protection

BRONZE2 S5 SRA Black

INDUSTRY-CONSTRUCTION & CIVIL ENGINEERING

High performance safety boots for the construction industry



Specific benefits



Comfort

- Stabilisation of the foot when walking
- Shock-absorbing heel to relieve joint strain
- Ergonomically designed footwear for comfortable wear



Performance

- Grip on the ground



Easy to use

- Rear lug for easy removal



Durability

- Sustainable materials

Certifications and norms



EN ISO 20345

S5 FO A E SRA

Applications

- Agriculture
- Public works
- Building
- Finishing works / Craftsmanship
- Heavy industry
- Light industry

Protects against risks



Antistatic



Shock



Slip



Weather



Foot protection

BRONZE2 S5 SRA Black

INDUSTRY-CONSTRUCTION & CIVIL ENGINEERING

High performance safety boots for the construction industry

Standards - Details

Technical details

Shoe type	Boot
Outsole material	Nitrile, PVC
Anti-perforation insert	Stainless steel
Upper material	PVC
Upper height size 42 (cm)	37.5
Calf circumference (cm)	45
Safety toe-cap	Stainless steel
Lining material	Polyester
Outsole finition	Injected
Weight (g per shoe)	1200
Size range	38 → 48



BRONZE2 S5 SRA

INDUSTRY-CONSTRUCTION & CIVIL ENGINEERING

High performance safety boots for the construction industry

Safety footwear

Logistics information

Reference	Colour	Size	Designation	EAN13	Box code			Weight			
BRON2S5NO38	Black	38	BRONZE2 S5 SRA	3295249258405	13295249258402	6	1	15.6 kg	40.0 cm	40.6 cm	35.0 cm
BRON2S5NO39	Black	39	BRONZE2 S5 SRA	3295249259327	13295249259324	6	1	15.6 kg	40.0 cm	40.6 cm	35.0 cm
BRON2S5NO40	Black	40	BRONZE2 S5 SRA	3295249259334	13295249259331	6	1	15.6 kg	40.0 cm	40.6 cm	35.0 cm
BRON2S5NO41	Black	41	BRONZE2 S5 SRA	3295249259341	13295249259348	6	1	15.6 kg	40.0 cm	40.6 cm	35.0 cm
BRON2S5NO42	Black	42	BRONZE2 S5 SRA	3295249259358	13295249259355	6	1	15.6 kg	40.0 cm	40.6 cm	35.0 cm
BRON2S5NO43	Black	43	BRONZE2 S5 SRA	3295249259365	13295249259362	6	1	15.6 kg	40.0 cm	40.6 cm	35.0 cm
BRON2S5NO44	Black	44	BRONZE2 S5 SRA	3295249259372	13295249259379	6	1	15.6 kg	40.0 cm	40.6 cm	35.0 cm
BRON2S5NO45	Black	45	BRONZE2 S5 SRA	3295249259389	13295249259386	6	1	15.6 kg	40.0 cm	40.6 cm	35.0 cm
BRON2S5NO46	Black	46	BRONZE2 S5 SRA	3295249259396	13295249259393	6	1	15.6 kg	40.0 cm	40.6 cm	35.0 cm
BRON2S5NO47	Black	47	BRONZE2 S5 SRA	3295249259402	13295249259409	6	1	15.6 kg	40.0 cm	40.6 cm	35.0 cm
BRON2S5NO48	Black	48	BRONZE2 S5 SRA	3295249259419	13295249259416	6	1	15.6 kg	40.0 cm	40.6 cm	35.0 cm
BRON2S5VE38	Green-Black	38	BRONZE2 S5 SRA	3295249257859	13295249257856	6	1	13.4 kg	42.4 cm	42.6 cm	34.4 cm
BRON2S5VE39	Green-Black	39	BRONZE2 S5 SRA	3295249259228	13295249259225	6	1	15.6 kg	40.0 cm	40.6 cm	35.0 cm
BRON2S5VE40	Green-Black	40	BRONZE2 S5 SRA	3295249259235	13295249259232	6	1	15.6 kg	42.0 cm	43.0 cm	33.8 cm
BRON2S5VE41	Green-Black	41	BRONZE2 S5 SRA	3295249259242	13295249259249	6	1	16.6 kg	41.0 cm	41.6 cm	37.4 cm
BRON2S5VE42	Green-Black	42	BRONZE2 S5 SRA	3295249259259	13295249259256	6	1	16.4 kg	42.6 cm	42.6 cm	33.6 cm
BRON2S5VE43	Green-Black	43	BRONZE2 S5 SRA	3295249259266	13295249259263	6	1	16.8 kg	41.0 cm	41.4 cm	38.0 cm
BRON2S5VE44	Green-Black	44	BRONZE2 S5 SRA	3295249259273	13295249259270	6	1	17.4 kg	41.4 cm	41.6 cm	37.0 cm
BRON2S5VE45	Green-Black	45	BRONZE2 S5 SRA	3295249259280	13295249259287	6	1	18.2 kg	41.6 cm	43.2 cm	37.2 cm
BRON2S5VE46	Green-Black	46	BRONZE2 S5 SRA	3295249259297	13295249259294	6	1	17.4 kg	41.0 cm	41.6 cm	37.2 cm
BRON2S5VE47	Green-Black	47	BRONZE2 S5 SRA	3295249259303	13295249259300	6	1	15.6 kg	40.0 cm	40.6 cm	35.0 cm
BRON2S5VE48	Green-Black	48	BRONZE2 S5 SRA	3295249259310	13295249259317	6	1	18.3 kg	41.4 cm	42.2 cm	37.2 cm
BRON2S5JA38	Yellow-Black	38	BRONZE2 S5 SRA	3295249258399	13295249258396	6	1	15.6 kg	40.0 cm	40.6 cm	35.0 cm
BRON2S5JA39	Yellow-Black	39	BRONZE2 S5 SRA	3295249259129	13295249259126	6	1	15.6 kg	40.0 cm	40.6 cm	35.0 cm
BRON2S5JA40	Yellow-Black	40	BRONZE2 S5 SRA	3295249259136	13295249259133	6	1	15.6 kg	40.0 cm	40.6 cm	35.0 cm



Safety footwear

BRONZE2 S5 SRA

INDUSTRY-CONSTRUCTION & CIVIL ENGINEERING

High performance safety boots for the construction industry

Logistics information

Reference	Colour	Size	Designation	EAN13	Box code			Weight			
BRON2S5JA41	Yellow-Black	41	BRONZE2 S5 SRA	3295249259143	13295249259140	6	1	15.6 kg	40.0 cm	40.6 cm	35.0 cm
BRON2S5JA42	Yellow-Black	42	BRONZE2 S5 SRA	3295249259150	13295249259157	6	1	15.6 kg	40.0 cm	40.6 cm	35.0 cm
BRON2S5JA43	Yellow-Black	43	BRONZE2 S5 SRA	3295249259167	13295249259164	6	1	15.6 kg	40.0 cm	40.6 cm	35.0 cm
BRON2S5JA44	Yellow-Black	44	BRONZE2 S5 SRA	3295249259174	13295249259171	6	1	15.6 kg	40.0 cm	40.6 cm	35.0 cm
BRON2S5JA45	Yellow-Black	45	BRONZE2 S5 SRA	3295249259181	13295249259188	6	1	15.6 kg	40.0 cm	40.6 cm	35.0 cm
BRON2S5JA46	Yellow-Black	46	BRONZE2 S5 SRA	3295249259198	13295249259195	6	1	15.6 kg	40.0 cm	40.6 cm	35.0 cm
BRON2S5JA47	Yellow-Black	47	BRONZE2 S5 SRA	3295249259204	13295249259201	6	1	15.6 kg	40.0 cm	40.6 cm	35.0 cm
BRON2S5JA48	Yellow-Black	48	BRONZE2 S5 SRA	3295249259211	13295249259218	6	1	15.6 kg	40.0 cm	40.6 cm	35.0 cm



Multiple sales



Minimum sales



Box Width



Box Depth



Box Height