

Datasheet

RS Stock No: 3044687

A4, 316 Stainless Steel Self-Colour Hexagon Socket Button Head Screws: Metric Thread



Button Head Socket Screws are designed for light duty with a similar thread design as a Socket Cap Screw although the dome shaped head is wider and has a lower profile than a Socket Cap Screw, presenting an aesthetic appearance to an assembly.

- A4 grade 316 Stainless Steel
- Threaded in accordance with ISO 7380 standard
- Used for applications with limited space in high tensile applications
- Higher level of corrosion resistance than A2 Stainless Steel
- Can be used up to 300°C
- Suitable for light fastening applications in most food, facilities maintenance and electronic & domestic applications.
- Typical applications include; Machine tooling, Securing guards and covers, Securing ornamental, fixtures, plus many more engineering applications
- Requires a Hex key / Allen key



ENGLISH

Please view our full range listing below for all A4, 316 Stainless Steel Self-Colour Hexagon Socket Button Head Screws.

Head Shape	Material	Stainless Steel Type	Thread Size	Length	RS Part No.
Hex Socket Button	Stainless Steel	A4, 316	M3	8 mm	2328142
Hex Socket Button	Stainless Steel	A4, 316	M3	10 mm	2328158
Hex Socket Button	Stainless Steel	A4, 316	M3	12 mm	2328164
Hex Socket Button	Stainless Steel	A4, 316	M4	8 mm	2328170
Hex Socket Button	Stainless Steel	A4, 316	M4	10 mm	2328186
Hex Socket Button	Stainless Steel	A4, 316	M4	12 mm	2328209
Hex Socket Button	Stainless Steel	A4, 316	M4	16 mm	2328215
Hex Socket Button	Stainless Steel	A4, 316	M5	10 mm	2328221
Hex Socket Button	Stainless Steel	A4, 316	M5	12 mm	2328237
Hex Socket Button	Stainless Steel	A4, 316	M5	16 mm	2328243
Hex Socket Button	Stainless Steel	A4, 316	M5	20 mm	2328265
Hex Socket Button	Stainless Steel	A4, 316	M5	25 mm	3044643
Hex Socket Button	Stainless Steel	A4, 316	M5	30 mm	3044659
Hex Socket Button	Stainless Steel	A4, 316	M5	40 mm	3044766
Hex Socket Button	Stainless Steel	A4, 316	M5	50 mm	3044744
Hex Socket Button	Stainless Steel	A4, 316	M6	12 mm	2328271
Hex Socket Button	Stainless Steel	A4, 316	M6	16 mm	2328287
Hex Socket Button	Stainless Steel	A4, 316	M6	20 mm	2328293
Hex Socket Button	Stainless Steel	A4, 316	M6	25 mm	2328300
Hex Socket Button	Stainless Steel	A4, 316	M6	30 mm	3044738
Hex Socket Button	Stainless Steel	A4, 316	M6	40 mm	3044722
Hex Socket Button	Stainless Steel	A4, 316	M6	50 mm	3044716
Hex Socket Button	Stainless Steel	A4, 316	M6	60 mm	3044700
Hex Socket Button	Stainless Steel	A4, 316	M8	12 mm	2328322
Hex Socket Button	Stainless Steel	A4, 316	M8	16 mm	2328338
Hex Socket Button	Stainless Steel	A4, 316	M8	20 mm	2328344
Hex Socket Button	Stainless Steel	A4, 316	M8	25 mm	2328350
Hex Socket Button	Stainless Steel	A4, 316	M8	30 mm	3044687
Hex Socket Button	Stainless Steel	A4, 316	M8	40 mm	3044671
Hex Socket Button	Stainless Steel	A4, 316	M8	50 mm	3044665
Hex Socket Button	Stainless Steel	A4, 316	M8	60 mm	3044772

