

# BMG758

## All-conditions grip glove with high cut resistance and sandy nitrile grip

A dexterous high cut resistance glove, glass and steel fibre free with excellent grip properties in all conditions thanks to the sandy nitrile finish.

### Features

- ▲ Cut resistance: Level D (EN 388:2016)
- ▲ A flexible and comfortable glove offering great dexterity
- ▲ Glass and steel fibre free reduce risks of irritation
- ▲ Nitrile sandy finish on palm provides a secure grip in light oily, greasy and dry conditions
- ▲ Flexible, close-fitting design for a comfortable wearing experience
- ▲ Breathable back of hand to reduce perspiration
- ▲ Seamless knit prevents irritation
- ▲ Elasticated wrist provides a secure fit

### Certifications



### Suitable industries & applications

#### Industries

- ▲ Aerospace
- ▲ Automotive
- ▲ Construction
- ▲ Manufacturing
- ▲ Highways and Infrastructure

#### Applications

- ▲ Machinery and Plant Operation
- ▲ Component and Product Assembly
- ▲ Vehicle Repairs and Maintenance
- ▲ Handling Sharp or Abrasive Materials
- ▲ General Maintenance



#### Europe

sales@globus.com  
+44 (0)161 877 4747  
+44 (0)161 877 4746

#### Middle East & Africa

sales.gcc@globusgroup.com  
+971 4 882 9962  
+971 4 882 9963

#### Americas

salesusa@globusgroup.com  
+1 83 337 54747

# BMG758

All-conditions grip glove with high cut resistance and sandy nitrile grip

### Product information

<b>Materials</b>	Liner:	13 Gauge High Strength Nylon
	Coating:	Sandy Nitrile
<b>Colour</b>	Grey / Black	
<b>Length</b>	253mm	
<b>Cuff Style</b>	Elasticated Knit Wrist	

### Ordering information

<b>XS</b>	BMG00758FB	Items per Pack 10 x Pairs
<b>S</b>	BMG00758FD	
<b>M</b>	BMG00758FF	Items per Case 120 x Pairs
<b>L</b>	BMG00758FH	
<b>XL</b>	BMG00758FJ	
<b>XXL</b>	BMG00758FL	

### Additional information

Certification legend



or click [here](#)

Declaration of conformity



or click [here](#)

View product online



or click [here](#)

#### Europe

sales@globus.com  
+44 (0)161 877 4747  
+44 (0)161 877 4746

#### Middle East & Africa

sales.gcc@globusgroup.com  
+971 4 882 9962  
+971 4 882 9963

#### Americas

salesusa@globusgroup.com  
+1 83 337 54747

**Globus Group**, T2 Trafford Point, Twining Road, Trafford Park, Manchester, M17 1SH, UNITED KINGDOM  
**Globus EMEA FZE**, Jafza One, Tower A, Office 2201, Jebel Ali, PO Box 61195, Dubai, UNITED ARAB EMIRATES  
**Globus Americas LLC**, 45 Rockefeller Plaza, Suite 2000, New York City, New York, 10111, USA

The descriptions, characteristics, applications and photos are given for information purposes and do not constitute a contractual commitment.  
The manufacturer reserves the right to make any modifications it deems necessary.