

# Product Data Sheet

## MaxiCut® Oil™ 34-450LP

|                         |  |
|-------------------------|--|
| <b>Colour – Coating</b> | Grey                                   |
| <b>Colour – Liner</b>   | Green                                  |
| <b>Design</b>           | Palm coated knitwrist                  |
| <b>Coating</b>          | NBR with Leather Pad                   |
| <b>Coating texture</b>  | Leather Pad                            |
| <b>Liner</b>            | UHMWPE-Glass-Nylon, Polyester, Spandex |
| <b>Patent number</b>    | EP 1 608 808                           |
| <b>Palm thickness</b>   | 2.50 mm                                |



### Dimensions

| Size Range                    | Size 8 (M) | Size 9 (L) | Size 10 (XL) |
|-------------------------------|------------|------------|--------------|
| Total glove length (+/-10 mm) | 220        | 230        | 240          |
| Wrist length (mm)             | 60         | 70         | 70           |
| Wrist width (mm)              | 75         | 80         | 82           |
| Palm width (+/-3 mm)          | 102        | 107        | 110          |
| Over lock colour              | Orange     | White      | Yellow       |

### EN test Results

| Test                    | Notified Body | Result/Pass |
|-------------------------|---------------|-------------|
| EN ISO 21420: 2020      | TÜV Rheinland | Yes         |
| EN 388: 2016 + A1: 2018 | TÜV Rheinland | 4342C       |
| EN 407: 2004            | TÜV Rheinland | X1XXXX      |



# Product Data Sheet

## MaxiCut® Oil™ 34-450LP

### Typical Performance Values

|  |               |
|--|---------------|
| EN 388:2016 + A1:2018 A. Abrasion Resistance | > 8000 Cycles |
| EN 388:2016 + A1:2018 B. Cut Resistance      | > 5.0 index   |
| EN 388:2016 + A1:2018 C. Tear Resistance     | > 75 newtons  |
| EN 388:2016 + A1:2018 D. Puncture Resistance | > 60 newtons  |
| EN 388:2016 + A1:2018 E. Cut Resistance ISO  | ≥ 10 Newton   |

### HandCare®

|  |           |
|--|-----------|
| Skin Health Alliance Dermatologically Accredited | Yes       |
| REACH compliant                                  | Yes       |
| Standard 100 by OEKO-TEX® (08.BH.57867)          | Certified |
| Washable   | 40°       |
| Sanitized®                                       | Yes       |



### Special features

|               |    |
|---------------|----|
| Silicone free | No |
|---------------|----|

### Packaging

|                        |                 |
|------------------------|-----------------|
| Pairs per poly bag     | 12              |
| Poly bags per carton   | 6               |
| Carton count           | 72              |
| Carton dimensions (mm) | 500 x 295 x 270 |



# Product Data Sheet

## MaxiCut® Oil™ 34-450LP

### Weight

| Size Range                      | Size 8 (M) | Size 9 (L) | Size 10 (XL) |
|---------------------------------|------------|------------|--------------|
| Glove weight / Pair (+/-6 gram) | 50         | 56         | 60           |
| Gross Weight (Kg)               | 4.7        | 5.2        | 5.5          |
| Carton Weight (Kg)              | 1          | 1          | 1            |
| Net Weight (Kg)                 | 3.7        | 4.2        | 4.5          |

Issue date: 07.06.2019

