


Data sheet

Commercial Art.No.: 91.020.1453.0

distributor GST15I2V 2P1T W BL02

gesis® MINI T-distributor, without mounting option, cascadable, number of poles 2, rated voltage 50 V, rated current 16 A, number of inputs 1, number of outputs 2, color of coding/ contact carrier light blue



Commercial Art.No.	91.020.1453.0
EAN	4049088225321
Order Unit	1

certificates / approvals



Technical data

general

rated current	16 A
rated voltage	50 V
rated impulse voltage	4 kV
pollution degree	2
mechanical coding	code 3
lockable	self-locking (unlocking by tool)
color of coding/ contact carrier	light blue
marking of poles	1, 2
RAL-number coding/insert connector	5012

model

number of inputs	1
number of outputs	2
type of fastening	no
degree of protection (IP)	IP20
type of distributor	T-distributor

material

housing material	polyamide
halogen free	yes
contact material	CuZn
fire load	0.034 kWh/St

surface finish	silver-plated
----------------	---------------

classification

ECLASS 11	
ECLASS 8.1	27440603
ETIM 9.0	EC002567
ETIM 8.0	EC002567
ETIM 7.0	EC002567
ETIM 6.0	EC002567
ETIM 5.0	EC002567
ETIM 4.0	EC002567

product compliance

ROHS conformity status	compliant/exempted
ROHS exceptions	III-6(c)
REACH-SVHC conformity status	Duty-To-Declare
REACH-SVHC substances	Lead
REACH-SVHC CAS numbers	7439-92-1




Accessories

Commercial Art.No.:	Article-type description:	Description:
07.418.9153.1	supporting plate GST15 h-/H-VT	geis®-Mounting plate for GST15 h- and H-distributors. for fastening to load-bearing, straight surfaces; fixing on cable trays with moulded expanding rivets; lying distributor mounting; color black


A
B
C
D
E
F

These dimensions will be especially checked at delivery
Only inspection dimensions
With /E marked dimensions are only valid for internal use

Diese Maße werden bei Abnahme besonders geprüft
Ausschließlich Prüfmaße
Mit /E gekennzeichnete Maße sind nur für interne Zwecke gültig



1:1



Tolerierung nach DIN 7167/Tolerance system acc. to DIN 7167. (This DIN-standard describes the envelope principle. According to the envelope principle the deviations of form and parallelism are limited by the size tolerances).					ja/yes ☒ Stoffverbots- und Deklarationsliste nach UU-TQM-05/03 ist einzuhalten. Conformity with Wieland document UU-TQM-05/03 (list of prohibited / declarable hazardous substances) to be declared!					
Freitoleranz nach General tolerance			CAD - Zeichnung, keine manuellen Änderungen CAD - drawing, no manual modifications allowed			1.Verwendung: First Use:		Blatt: 1 von 1 Sheet: 1 of 1		
	/		Werkstoff/Material Farbe/colour: lichtblau/lightblue		2013	Tag/Date	Name	Zeichnung Nr./Drawing No. 91.020.1453.0 01K		Index
	/				gezeichnet drawn	24.09.	Ritter			
	/				geprüft checked	-	-			
	/				Normgepr. Stand. check	-	-			
Maßstab/Scale 2:1					Maße in mm/Dimensions are in mm					
Vol.			mm³	Ofl./Surf.	mm²	Ersatz für/Replacement for: -				
Index					Type		Benennung/Title T-VERTEILER T-distributor GST1512			
Datum / Blatt Date / Sheet										
Änderung/Revision										

Weitergabe sowie Vervielfältigung dieses Dokuments, Verwertung und Mitteilung seines Inhalts sind verboten, soweit nicht ausdrücklich gestattet. Die Reproduktion, Distribution und Utilization of this document as well as the communication of its contents to others without express authorization is prohibited.