

Crimping pliers - CRIMPFOX-RCI 6 - 1212057

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Crimping pliers, for insulated cable lugs, 0.5 mm² ... 6.0 mm² (red, blue, yellow), oval crimp, symmetrical

Why buy this product

- CRIMPFOX-RCI 6 /... represent the top end of the range for cable lug crimping pliers
- Precision-manufactured dies ensure consistently high levels of quality during contact processing
-



Key commercial data

Packing unit	1 pc
GTIN	 4 046356 453929
Weight per Piece (excluding packing)	99.99 g
Custom tariff number	82032000
Country of origin	Sweden

Technical data

Dimensions

Length (b)	256 mm
Height	68 mm
Width (a)	25 mm

General

Color	black
Compression	Oval crimp
Type of contact	Insulated cable lugs
Designation	Crimping position 1
Min. cross section	0.5 mm ²
Max. cross section	1.5 mm ²

Crimping pliers - CRIMPFOX-RCI 6 - 1212057

Technical data

General

AWG min	20
AWG max	16
Designation	Crimping position 2
Min. cross section	1.5 mm ²
Max. cross section	2.5 mm ²
AWG min	16
AWG max	14
Designation	Crimping position 3
Min. cross section	2.5 mm ²
Max. cross section	6 mm ²
AWG min	14
AWG max	10
Die station	Crimping position 4
	Crimping position 5

Classifications

eCl@ss

eCl@ss 4.0	21040301
eCl@ss 4.1	21040301
eCl@ss 5.0	21040301
eCl@ss 5.1	21040301
eCl@ss 6.0	21043811
eCl@ss 7.0	21043811

ETIM

ETIM 2.0	EC001186
ETIM 3.0	EC001186
ETIM 4.0	EC001186
ETIM 5.0	EC000168

UNSPSC

UNSPSC 6.01	27112118
UNSPSC 7.0901	27111518
UNSPSC 11	23171604
UNSPSC 12.01	27111518
UNSPSC 13.2	27111518

Approvals

Approvals

Crimping pliers - CRIMPFOX-RCI 6 - 1212057

Approvals

Approvals

EAC

Ex Approvals

Approvals submitted

Approval details

EAC

Accessories

Accessories

Die

Replacement die - CRIMPFOX-RCI 6/DIE - 1212058



Spare die for CRIMPFOX-RCI 6

Mounting material

Replacement spring - CRIMPFOX/ SPR-1 - 1212069



Spare recuperating spring
