

## **FEATURES**

- 5 pieces ESD pliers set:
- 1 flush medium cutter, max cut Ø 1.30mm-16 awg. ESD-safe version
- 1 long serrated flatnose pliers. ESD-safe version
- 3 ESD tweezers. Models: 7 ESD very fine curved tips, 5 ESD very fine and sharp tips, 2A ESD Flat rounded tips.
- In durable ESD wallet roll
- Ergonomic anti-slip bicomponent handle for a safe, light and comfortable grip
- Anti-reflection phosphating surface treatment
- Laser marking
- Made in Italy

# RS PRO 5 pieces ESD set: 1 cutter, 1 pliers, 3 tweezers

**RS PRO Stock No.: 249-8655** 



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

rs pro

#### **Product Description**

- The tools are joined with grounded holes and surfaces, thereby allowing precise movements.
- The anti-slip bi-material dolphin handle is created following ergonomic principles, thus guaranteeing a safe, light and comfortable grip for the operator even when used constantly for many hours
- This tools set is ideal for different applications in microelectronics, jewellery making, laboratory, watch making and repairs, DIY. In durable ESD wallet roll

#### **General Specifications**

| 1 ESD MEDIUM CUTTER        |  |  |
|----------------------------|--|--|
| Cutter Type                | Medium head. Flush cut.                                  |  |
| Non-Sparking               | Yes  |  |
| Tip Style                  | Flush cut. Medium head size                              |  |
| Material                   | Carbon steel   |  |
| Finish                     | Anti-reflection phosphating surface treatment, grey grip |  |
| Overall Length             | 138 mm   |  |
| Cutting Force              | 5.5 kg   |  |
| Steel Thickness            | 3 mm   |  |
| Max cut                    | Ø 1.30mm - 16 awg copper wire                            |  |
| 1 ESD LONG PLIERS          |  |  |
| Non-Sparking               | Yes  |  |
| Tip Style                  | Long serrated flat-nose pliers                           |  |
| Material                   | Carbon steel   |  |
| Finish                     | Anti-reflection phosphating surface treatment, grey grip |  |
| Overall Length             | 160 mm   |  |
| HRC                        | 48-50  |  |
| Weight                     | 78 g   |  |
| Steel Thickness            | 3 mm   |  |
| 1 ESD TWEEZERS MODEL 7 ESD |  |  |
| Overall length (mm)        | 120  |  |
| Overall length (")         | 4 3/4"   |  |
| Point Type                 | very fine curved tips                                    |  |
| Anti-magnetic              | Yes  |  |
| Anti-acid                  | Yes  |  |
| ESD                        | Yes  |  |



| 1 ESD TWEEZERS MODEL 5 ESD  |                          |  |
|-----------------------------|--------------------------|--|
| Overall length (mm)         | 110                      |  |
| Overall length (")          | 4 1/4"                   |  |
| Point Type                  | very fine and sharp tips |  |
| Anti-magnetic               | Yes                      |  |
| Anti-acid                   | Yes                      |  |
| ESD                         | Yes                      |  |
| 1 ESD TWEEZERS MODEL 2A ESD |                          |  |
| Overall length (mm)         | 120                      |  |
| Overall length (")          | 4 3/4"                   |  |
| Point Type                  | Flat rounded tips        |  |
| Anti-magnetic               | Yes                      |  |
| Anti-acid                   | Yes                      |  |
| ESD                         | Yes                      |  |

| Electrical Specifications |     |  |
|---------------------------|-----|--|
|                           |     |  |
| ESD Safe                  | YES |  |

### Kit contains

| Name                               | QTY | RSPRO order code |
|------------------------------------|-----|------------------|
| ESD flush cutter- medium head      | 1   | 245-0491         |
| ESD long serrated flat-nose pliers | 1   | 249-8672         |
| ESD tweezers international code 2A | 1   | 238-0687         |
| ESD tweezers international code 5  | 1   | 238-0703         |
| ESD tweezers international code 7  | 1   | 238-0708         |

## Tools set



