



Pin punch

108



Product no. **70070001**
GTIN **4018754040612**
Model **108/150 x 2,5**

Label. Pin punch Tip dia.2,5mm L.150mm

Properties.

- octagonal
- Chrome Alloy Steel, painted silver
- DIN 6450

Technical attributes.

DIN	DIN 6450
Diameter of tool tip	2,5 mm
Length mm (L)	150 mm
Size tool shank 8-edge	10 mm

Logistics data.

Depth mm (IFS)	151
Width mm (IFS)	11
Height mm (IFS)	11
WEEE/ElektroG	nicht ear-pflichtig
Length (packaged, mm)	165
Width (packaged, mm)	59
Height (packaging, mm)	25
Volume (packaged, dm3)	0.243375 dm3
Product no.	70070001
Weight (gross, kg)	0,650
Weight PAP (kg)	0,160
Weight PVC (kg)	0,000
GTIN	4018754040612
Country of origin AWR	GERMANY
Region of origin	Nordrhein-Westfalen
Customs tariff no.	82055980
Packing standard	10
Weight (g)	65 g

Variants.

Product no.	Model No. (ERP)	Description	GTIN
70071152	108/115 x 2	Pin punch Tip dia.2mm L.115mm	4018754040742
70070013	108/125 x 3	Pin punch Tip dia.3mm L.125mm	4018754040728
70070001	108/150 x 2,5	Pin punch Tip dia.2,5mm L.150mm	4018754040612
70070002	108/150 x 3	Pin punch Tip dia.3mm L.150mm	4018754040629
70070003	108/150 x 4	Pin punch Tip dia.4mm L.150mm	4018754040636
70070004	108/150 x 5	Pin punch Tip dia.5mm L.150mm	4018754040643
70070005	108/150 x 6	Pin punch Tip dia.6mm L.150mm	4018754040650
70070006	108/150 x 8	Pin punch Tip dia.8mm L.150mm	4018754040667
70070009	108/175 x 3	Pin punch Tip dia.3mm L.175mm	4018754040681
70070010	108/175 x 4	Pin punch Tip dia.4mm L.175mm	4018754040698
70070012	108/175 x 6	Pin punch Tip dia.6mm L.175mm	4018754040711
70070008	108/200 x 8	Pin punch Tip dia.8mm L.200mm	4018754040674
70070011	108/200 x 10	Pin punch Tip dia.10mm L.200mm	4018754040704

GTIN.



STAHLWILLE Eduard Wille GmbH

Lindenallee 27 · 42349 Wuppertal · Germany · Phone: +49 202 4791-0

info@stahlwille.de · www.stahlwille.com

© STAHLWILLE Eduard Wille GmbH, Wuppertal