

AP65 - Grip 15 Nitrile Foam Texpel Glove

Collection: General Handling

Range: Hand Protection

Materials: Nylon, Latex Free Elastane

Dipping:

Inner Pack: 12

Outer Carton: 144

Product information

The ultimate in comfort, fit and durability. Nylon and elastane liner hugs the hand whilst wicking away unwanted moisture. The premium foam nitrile coating provides excellent abrasion resistance. Treated with an anti-microbial finish to ensure that the gloves stay fresher for longer.

General Handling

The general handling and grip glove category is one of the most popular collections within the Portwest hand protection range. A carefully selected range of coatings, including latex, nitrile, polyurethane and PVC, provides a broad range of styles suited to a diverse range of tasks.

Hand Protection

A wide and increasing range of hand protection products is available. In order to help cater to every need. Only the best materials and manufacturing methods are used in the production of Portwests' extensive range of Hand Protection products....

Standards

EN ISO 21420: 2020 Dexterity 5

EN 388: 2016 + A1: 2018 (4131A)

ANSI/ISEA 105: 2016 CUT Level (A1)

ANSI/ISEA 105: 2016 ABRASION Level (6)

ANSI/ISEA 105: 2016 PUNCTURE Level (2)



Features

- Nitrile foam coating for excellent grip in wet and dry conditions
- Nylon's high tensile strength with additional stretch for an improve fit
- Anti-microbial finish Texpel Micro, kills 99.9% of bacteria
- 15 gauge liner provides the best balance of dexterity and durability
- 100% latex free
- Breathable seamless lining ideal for precision handling in dry environments
- OEKO-TEX® STANDARD 100 approved
- Retail tag which aids presentation for retail sales
- CE certified



PRODUCT SPECIFICATION & TECHNICAL DATASHEET

AP65 - Grip 15 Nitrile Foam Texpel Glove

Commodity Code: 6116102091

Test House

CTC (Notified Body No.: 0075)

4, rue Hermann Frenkel

Cedex 07, France

Cert No: 0075/2085/162/10/20/2668

SATRA Technology Centre Ltd (Notified Body No.: AB: 0321)

SATRA Technology Park

NN16 8SD, United Kingdom

Cert No: AB0321/20364-01/E00-00

Carton Dimensions/Weight

Item	Colour	Len	Wid	Hgt	Weight(Kg)	Cubic(m ³)	EAN13	GTIN/DUN14
AP65K7RXS	Black/Grey	60.0	30.0	22.0	0.0330	0.0396	5036108338801	25036108827453
AP65K7RS	Black/Grey	60.0	30.0	22.0	0.0340	0.0396	5036108338788	25036108827439
AP65K7RM	Black/Grey	60.0	30.0	22.0	0.0360	0.0396	5036108338771	25036108827422
AP65K7RL	Black/Grey	60.0	30.0	22.0	0.0420	0.0396	5036108338764	25036108827415
AP65K7RXL	Black/Grey	60.0	30.0	22.0	0.0480	0.0396	5036108338795	25036108827446
AP65K7RXXL	Black/Grey	60.0	30.0	22.0	0.0500	0.0396	5036108338818	25036108827460