

## Specialty Tapes

### Double Coated Tapes (cont.)

#### 3M™ Double Coated Urethane Foam Tapes 4004, 4008, 4016, 4026 and 4032

- 1/32" to 1/4" thicknesses.
- This tape has an acrylic adhesive that seals, cushions vibrations, resists impacts, and insulates.
- It adheres to most clean, dry, rough, or smooth surfaces.
- Resists heat up to 380° F for short periods and 225° F for an extended time.



UPC Number	Size	Quantity Per Case
<b>4004</b>		
021200-03392-6	1/2" x 18 yds.	18
021200-03393-3	3/4" x 18 yds.	12
021200-03394-0	1" x 18 yds.	9
<b>4008</b>		
051131-06439-3	1" x 4 yds.	5
021200-06450-0	1/2" x 36 yds.	18
021200-06451-7	3/4" x 36 yds.	12
021200-06452-4	1" x 36 yds.	9
<b>4016</b>		
021200-06453-1	1/2" x 36 yds.	18
021200-06454-8	3/4" x 36 yds.	12
021200-06455-5	1" x 36 yds.	9
<b>4026</b>		
051131-06440-9	1" x 6 yds.	5
<b>4032</b>		
021200-06456-2	1/2" x 72 yds.	18
021200-06457-9	3/4" x 72 yds.	12
021200-06458-6	1" x 72 yds.	9

#### 3M™ Double Coated Urethane Foam Tapes 4052, 4056, 4082 and 4084

- 1/32" to 1/4" thicknesses.
- This tape has an acrylic adhesive that seals, cushions vibrations, resists impacts, and insulates.
- It adheres to most clean, dry, rough, or smooth surfaces.
- Resists heat up to 380°F for short periods and 225°F for an extended time.



UPC Number	Color	Size	Quantity Per Case
<b>4052</b>			
021200-14667-1	Black	1/2" x 72 yds.	18
021200-14618-3	Black	3/4" x 72 yds.	12
021200-14557-5	Black	1" x 72 yds.	9
<b>4056</b>			
021200-14668-8	Black	1/2" x 36 yds.	18
021200-14619-0	Black	3/4" x 36 yds.	12
021200-14558-2	Black	1" x 36 yds.	9
<b>4082</b>			
021200-25217-4	Off-White	1/2" x 72 yds.	18
021200-25218-1	Off-White	3/4" x 72 yds.	12

### 3M™ Double Coated Urethane Foam Tapes 4052, 4056, 4082 and 4084 (cont.)

UPC Number	Color	Size	Quantity Per Case
<b>4084</b>			
021200-25219-8	Off-White	1/2" x 36 yds.	18
021200-25220-4	Off-White	3/4" x 36 yds.	12
021200-24393-6	Off-White	1" x 36 yds.	9

#### 3M™ Double Coated Urethane Foam Tape 4085

- 1/32 of an inch to 1/4 of an inch thicknesses.
- This tape has a rubber adhesive that seals, cushions vibrations, resists impacts, and insulates.
- Very good initial tack and peel strength.
- It adheres to most clean, dry, rough, or smooth surfaces.
- Off white color.
- Resists heat up to 200°F for short periods and 150°F for an extended time.



UPC Number	Size	Quantity Per Case
021200-17660-9	1/2" x 72 yds.	18
021200-17661-6	3/4" x 72 yds.	12
021200-17662-3	1" x 72 yds.	9

#### 3M™ Double Coated Vinyl Foam Tape 4408

- Its bond is very strong with great peel strength.
- Has an acrylic adhesive and is very flexible so it easily conforms to corners.
- Replaces the need of drills and screws.
- It seals, cushions vibrations, and resists solvents.
- Great for bonding fiberglass trim panels or signs in buildings.
- It adheres to most rough, or smooth surfaces.
- Resists heat up to 200°F for short periods and 150°F for weeks.
- Comes in 1/32" or 1/16" thicknesses, 3 widths, and in black or white.



UPC Number	Size	Quantity Per Case
021200-03289-9	1/2" x 36 yds.	18
021200-03290-5	3/4" x 36 yds.	12
021200-03291-2	1" x 36 yds.	9