



SITOR cylindrical fuse link, 22x127 mm, 16 A, gS, Un AC: 1500 V, Un DC: 1000 V

Figure similar

| Model                                    |                             |             |
|------------------------------------------|-----------------------------|-------------|
| product brand name                       | SETRON                      |             |
| product designation                      | SITOR cylindrical fuse link |             |
| General technical data                   |                             |             |
| operating class of the fuse link         | gS                          |             |
| type of voltage of the operating voltage | AC                          |             |
| supply voltage at DC                     | 1 000 V                     |             |
| Main circuit                             |                             |             |
| operational current rated value          | 16 A                        |             |
| Product details                          |                             |             |
| product component striker                | No                          |             |
| Mechanical Design                        |                             |             |
| mounting position                        | Any, preferably vertical    |             |
| net weight                               | 104 g                       |             |
| Approvals Certificates                   |                             |             |
| General Product Approval                 | other                       | Environment |




[Confirmation](#)

[Environmental Con-  
firmations](#)

[Environmental Con-  
firmations](#)

| Further information                                                                                                                                                                                                                                          |
|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Information on the packaging<br><a href="https://support.industry.siemens.com/cs/ww/en/view/109813875">https://support.industry.siemens.com/cs/ww/en/view/109813875</a>                                                                                      |
| Information- and Downloadcenter (Catalogs, Brochures,...)<br><a href="http://www.siemens.com/lowvoltage/catalogs">http://www.siemens.com/lowvoltage/catalogs</a>                                                                                             |
| Industry Mall (Online ordering system)<br><a href="https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3NC2316-0MK">https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3NC2316-0MK</a>                                          |
| Service&Support (Manuals, Certificates, Characteristics, FAQs,...)<br><a href="https://support.industry.siemens.com/cs/ww/en/ps/3NC2316-0MK">https://support.industry.siemens.com/cs/ww/en/ps/3NC2316-0MK</a>                                                |
| Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)<br><a href="http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3NC2316-0MK">http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3NC2316-0MK</a> |
| CAX-Online-Generator<br><a href="http://www.siemens.com/cax">http://www.siemens.com/cax</a>                                                                                                                                                                  |
| Tender specifications<br><a href="http://www.siemens.com/specifications">http://www.siemens.com/specifications</a>                                                                                                                                           |



last modified:

4/11/2025 

