

# Professional Cable Reel 300 KU 4100 IP 44, 40 m H07RN-F 3G1,5

For construction site use in accordance with DGUV 203-006 (formerly BGI 608) and permanent outdoor use, IP 44.



**MADE IN  
GERMANY**

**+ CABLE  
PILOT**

**5 YEARS  
MANUFACTURER  
GUARANTEE**

**DGUV-I  
203-006  
K2**

**VDE 0100  
Teil 704**

**SPECIAL  
ROBUST**

**IP 44**

**Product number** 9231400101  
**EAN** 4007123688609

## DESCRIPTION

- Reel body made of special plastic on galvanised support frame.
- 5 splash-proof sockets with earthing contact, with self-closing lids.
- Innovative „cablepilot“ carrying handle for perfect cable routing. Swings on both sides for convenient carrying and hanging.
- With twist handle for convenient retraction.
- With drum brake.
- Category 2 equipment (K2 DGUV 203-005): Use for rough operation with high mechanical, physical and chemical impacts.
- RN cable is approved for harsh building conditions in accordance with VDE 0100 Part 704.
- Overheating protection with indicator light for overheating and overloading.
- With visual readiness indicator.

## TECHNICAL DATA

|                               |                 |                                       |                                                   |
|-------------------------------|-----------------|---------------------------------------|---------------------------------------------------|
| <b>Cable quality</b>          | Rubber-Neoprene | <b>Plug system socket</b>             | Type F (Protective contact)                       |
| <b>Cable length</b>           | 40 m            | <b>Plug system plug</b>               | Type E and F (Protective contact with earth hole) |
| <b>Cable designation</b>      | H07RN-F 3G1,5   | <b>Max. current carrying capacity</b> | 16 A                                              |
| <b>Cable colour</b>           | black           | <b>Nominal input voltage</b>          | 230 V                                             |
| <b>Reel diameter</b>          | 300 mm          | <b>Degree of protection (IP)</b>      | IP44                                              |
| <b>Plug system CEE socket</b> | Without         |                                       |                                                   |

## PACKAGING, DIMENSIONS AND WEIGHTS

|                                              |                         |                                                |                         |
|----------------------------------------------|-------------------------|------------------------------------------------|-------------------------|
| <b>UP</b>                                    | 1                       | <b>Weight of product (including packaging)</b> | 7.61 kg                 |
| <b>Weight of product (without packaging)</b> | 7.61 kg                 | <b>Dimension LxWxH (incl. packing)</b>         | 20.5 cm x 31 cm x 40 cm |
| <b>Dimension LxWxH (without packing)</b>     | 20 cm x 30 cm x 39.5 cm |                                                |                         |

## SCOPE OF DELIVERY

Professional Cable reel 300 KU 4100 IP44