









RS Pro 21mm IP68 Connectors

(Please see pages 2 and 3 for details of right-angled cable-mount connectors and in-line mating sets)


Straight Cable-Mount Connector					In-Line Cable Connector					Rear-Nut Panel-Mount Connector					2-Hole Flange-Mount Connector			
																		
RS Stock No:	No. of Contacts	Terminal Style	Gender		RS Stock No:	No. of Contacts	Terminal Style	Gender	Or	RS Stock No:	No. of Contacts	Terminal Style	Gender	Or	RS Stock No:	No. of Contacts	Terminal Style	Gender
131-6382	2	Solder	Female	Mates with	131-6362	2	Solder	Male	Or	131-6370	2	Solder	Male	Or	131-6378	2	Solder	Male
124-6683	2	Screw	Female	"	124-6668	2	Screw	Male	"	124-6674	2	Screw	Male	"	124-6680	2	Screw	Male
131-6383	3	Solder	Female	"	131-6363	3	Solder	Male	"	131-6371	3	Solder	Male	"	131-6379	3	Solder	Male
124-6684	3	Screw	Female	"	124-6669	3	Screw	Male	"	124-6675	3	Screw	Male	"	124-6681	3	Screw	Male
131-6384	4	Solder	Female	"	131-6364	4	Solder	Male	"	131-6372	4	Solder	Male	"	131-6380	4	Solder	Male
207-2213	4	Screw	Female	"	207-2214	4	Screw	Male	"	207-2217	4	Screw	Male	"	207-2219	4	Screw	Male
131-6385	5	Solder	Female	"	131-6365	5	Solder	Male	"	131-6373	5	Solder	Male	"	131-6381	5	Solder	Male
124-6685	5	Screw	Female	"	124-6670	5	Screw	Male	"	124-6676	5	Screw	Male	"	124-6682	5	Screw	Male
144-4148	5C	Solder	Female	"	144-4143	5C	Solder	Male	"	144-4145	5C	Solder	Male	"	144-4147	5C	Solder	Male
144-4211	7	Solder	Female	"	144-4196	7	Solder	Male	"	144-4202	7	Solder	Male	"	144-4208	7	Solder	Male
144-4212	9	Solder	Female	"	144-4197	9	Solder	Male	"	144-4203	9	Solder	Male	"	144-4209	9	Solder	Male
144-4213	12	Solder	Female	"	144-4198	12	Solder	Male	"	144-4204	12	Solder	Male	"	144-4210	12	Solder	Male
131-6386	2	Solder	Male	Mates with	131-6358	2	Solder	Female	Or	131-6366	2	Solder	Female	Or	131-6374	2	Solder	Female
124-6686	2	Screw	Male	"	124-6664	2	Screw	Female	"	124-6671	2	Screw	Female	"	124-6677	2	Screw	Female
131-6387	3	Solder	Male	"	131-6359	3	Solder	Female	"	131-6367	3	Solder	Female	"	131-6375	3	Solder	Female
124-6687	3	Screw	Male	"	124-6665	3	Screw	Female	"	124-6672	3	Screw	Female	"	124-6678	3	Screw	Female
131-6388	4	Solder	Male	"	131-6360	4	Solder	Female	"	131-6368	4	Solder	Female	"	131-6376	4	Solder	Female
207-2212	4	Screw	Male	"	207-2216	4	Screw	Female	"	207-2218	4	Screw	Female	"	207-2220	4	Screw	Female
131-6389	5	Solder	Male	"	131-6361	5	Solder	Female	"	131-6369	5	Solder	Female	"	131-6377	5	Solder	Female
124-6688	5	Screw	Male	"	124-6666	5	Screw	Female	"	124-6673	5	Screw	Female	"	124-6679	5	Screw	Female
144-4149	5C	Solder	Male	"	144-4141	5C	Solder	Female	"	144-4144	5C	Solder	Female	"	144-4146	5C	Solder	Female
144-4214	7	Solder	Male	"	144-4193	7	Solder	Female	"	144-4199	7	Solder	Female	"	144-4205	7	Solder	Female
144-4215	9	Solder	Male	"	144-4194	9	Solder	Female	"	144-4200	9	Solder	Female	"	144-4206	9	Solder	Female
144-4216	12	Solder	Male	"	144-4195	12	Solder	Female	"	144-4201	12	Solder	Female	"	144-4207	12	Solder	Female
Use Sealing Cap No: 207-0653					Use Sealing Cap No: 207-0654					Use Sealing Cap No: 207-0654					Use Sealing Cap No: 207-0654			

RS Pro 21mm IP68 Connectors

Right-Angled Cable-Mount Connector					In-Line Cable Connector					Rear-Nut Panel-Mount Connector					2-Hole Flange-Mount Connector			
RS Stock No:	No. of Contacts	Terminal Style	Gender		RS Stock No:	No. of Contacts	Terminal Style	Gender		RS Stock No:	No. of Contacts	Terminal Style	Gender		RS Stock No:	No. of Contacts	Terminal Style	Gender
207-2235	2	Solder	Female	Mates with	131-6362	2	Solder	Male	Or	131-6370	2	Solder	Male	Or	131-6378	2	Solder	Male
207-2236	2	Screw	Female	"	124-6668	2	Screw	Male	"	124-6674	2	Screw	Male	"	124-6680	2	Screw	Male
207-2237	3	Solder	Female	"	131-6363	3	Solder	Male	"	131-6371	3	Solder	Male	"	131-6379	3	Solder	Male
207-2238	3	Screw	Female	"	124-6669	3	Screw	Male	"	124-6675	3	Screw	Male	"	124-6681	3	Screw	Male
207-2239	4	Solder	Female	"	131-6364	4	Solder	Male	"	131-6372	4	Solder	Male	"	131-6380	4	Solder	Male
207-2240	4	Screw	Female	"	207-2214	4	Screw	Male	"	207-2217	4	Screw	Male	"	207-2219	4	Screw	Male
207-2242	5	Solder	Female	"	131-6365	5	Solder	Male	"	131-6373	5	Solder	Male	"	131-6381	5	Solder	Male
207-2243	5	Screw	Female	"	124-6670	5	Screw	Male	"	124-6676	5	Screw	Male	"	124-6682	5	Screw	Male
207-2241	5C	Solder	Female	"	144-4143	5C	Solder	Male	"	144-4145	5C	Solder	Male	"	144-4147	5C	Solder	Male
207-2244	7	Solder	Female	"	144-4196	7	Solder	Male	"	144-4202	7	Solder	Male	"	144-4208	7	Solder	Male
207-2245	9	Solder	Female	"	144-4197	9	Solder	Male	"	144-4203	9	Solder	Male	"	144-4209	9	Solder	Male
207-2234	12	Solder	Female	"	144-4198	12	Solder	Male	"	144-4204	12	Solder	Male	"	144-4210	12	Solder	Male
207-2223	2	Solder	Male	Mates with	131-6358	2	Solder	Female	Or	131-6366	2	Solder	Female	Or	131-6374	2	Solder	Female
207-2224	2	Screw	Male	"	124-6664	2	Screw	Female	"	124-6671	2	Screw	Female	"	124-6677	2	Screw	Female
207-2225	3	Solder	Male	"	131-6359	3	Solder	Female	"	131-6367	3	Solder	Female	"	131-6375	3	Solder	Female
207-2226	3	Screw	Male	"	124-6665	3	Screw	Female	"	124-6672	3	Screw	Female	"	124-6678	3	Screw	Female
207-2227	4	Solder	Male	"	131-6360	4	Solder	Female	"	131-6368	4	Solder	Female	"	131-6376	4	Solder	Female
207-2228	4	Screw	Male	"	207-2216	4	Screw	Female	"	207-2218	4	Screw	Female	"	207-2220	4	Screw	Female
207-2230	5	Solder	Male	"	131-6361	5	Solder	Female	"	131-6369	5	Solder	Female	"	131-6377	5	Solder	Female
207-2231	5	Screw	Male	"	124-6666	5	Screw	Female	"	124-6673	5	Screw	Female	"	124-6679	5	Screw	Female
207-2229	5C	Solder	Male	"	144-4141	5C	Solder	Female	"	144-4144	5C	Solder	Female	"	144-4146	5C	Solder	Female
207-2232	7	Solder	Male	"	144-4193	7	Solder	Female	"	144-4199	7	Solder	Female	"	144-4205	7	Solder	Female
207-2233	9	Solder	Male	"	144-4194	9	Solder	Female	"	144-4200	9	Solder	Female	"	144-4206	9	Solder	Female
207-2222	12	Solder	Male	"	144-4195	12	Solder	Female	"	144-4201	12	Solder	Female	"	144-4207	12	Solder	Female
Use Sealing Cap No: 207-0653					Use Sealing Cap No: 207-0654					Use Sealing Cap No: 207-0654					Use Sealing Cap No: 207-0654			

RS Pro 21mm IP68 Connectors



Connector Sets (Straight Cable-Mount Plug & In-Line Socket)			
RS Stock No:	No. of Contacts	Terminal Style	
131-6393	2	Solder	Equivalent to 131-6386 Plug + 131-6358 Socket
131-6391	3	Solder	Equivalent to 131-6387 Plug + 131-6359 Socket
124-6693	3	Screw	Equivalent to 124-6687 Plug + 124-6665 Socket
131-6390	4	Solder	Equivalent to 131-6389 Plug + 131-6360 Socket
124-6692	4	Screw	Equivalent to 207-2212 Plug + 207-2216 Socket
131-6392	5	Solder	Equivalent to 131-6389 Plug + 131-6361 Socket
124-6694	5	Screw	Equivalent to 124-6688 Plug + 124-6666 Socket
144-4150	5C	Solder	Equivalent to 144-4149 Plug + 144-4141 Socket
144-4221	7	Solder	Equivalent to 144-4214 Plug + 144-4193 Socket
144-4222	9	Solder	Equivalent to 144-4215 Plug + 144-4194 Socket
144-4223	12	Solder	Equivalent to 144-4216 Plug + 144-4195 Socket