

1500 PLUS Stitched - Model 111

Particle-filtering, anti-static SMS protective suit, delivering light chemical resistance

Previously known as: MICROGARD 1500 PLUS - Model 111

Particle-filtering, anti-static SMS protective suit, delivering light chemical resistance.

- **Specialized protection:** The AlphaTec® 1500 PLUS Stitched - Model 111 delivers light chemical resistance*, guards against asbestos and filters 99.9% of particles over 3 microns in size, as well as brick and cement dust, light aerosols and mists
- **Heightened breathability:** This asbestos protection suit's air and water vapor permeability also reduces wearers' exposure to heat stress
- **Enhanced fit and features:** Wearer comfort is augmented by this protective body suit's optimal fit, while a three-piece hood offers additional protective coverage, finger loops offer a secure hold.
- **Certified antistatic capabilities:** The AlphaTec® 1500 PLUS Stitched - Model 111 is tested against EN 1149-5 antistatic standards

*this protective suit offers CE Category III Type 5/6 protection



Industries

- Machinery and Equipment
- Life Sciences
- Metal fabrication
- Construction
- Chemical

Applications


- Unpacking of bulk goods
- Loading and unloading of process equipment
- Body Surface checking, marking and touching up
- Assembly & inspection of components
- Painting or cleaning tools or robots
- Production line support & maintenance

KEY FEATURES & BENEFITS

- **Particle-filtering SMS fabric:** Filters 99.9% of particles over 3 microns*
- **Air and water vapor permeability:** Ensures heat stress protection
- **Optimised body fit:** Enhanced comfort

*According to the KAKEN particle penetration test

Material Diagram



Seam Diagram



Performance Standards


0598


EN 1073-2


EN 1149-5

EN ISO 13688:2013


TYPE 5


TYPE 6

Product Information

Product Information	
Available Sizes	S, M, L, XL, 2XL
Color	White, Blue, Navy, Orange
Country Of Origin	Bangladesh, China, Sri Lanka
Models Available	103, 113
Packaging Overview	Individually Packed
Product Material	SMS fabric with anti-static treatment
Product Reference	1500 PLUS Stitched - Model 111
Standards Overview	CE CATEGORY III (Type 5, Type 6, EN 1073-2, EN 1149-5)
Seam Type	Stitched
Shelf Life	5 Years
Style Number	W15S111, B15S11, N15S111, O15S111

Suit components & accessories

Suit Components and Accessories	
Design Features	Coverall with 3-piece hood, 2-way front zipper with re-sealable storm flap and finger loops. Elasticated hood, wrists, waist and ankles.

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region
Ansell Healthcare Europe NV
T: +32 (0) 2 528 74 00

North America Region
Ansell Healthcare Products LLC
T: +1 800 800 0444

Australia
Ansell Limited
T: +61 1800 337 041

Asia Pacific Region
Ansell Global Trading Center
T: +603 8310 6688

Latin America & Caribbean Region
Ansell Commercial Mexico S.A. de C.V.
T: +52 442 248 1544 / 248 3133

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

